

# PC 6/ 6-STF-10,16 - PCB connector

1913617

<https://www.phoenixcontact.com/us/products/1913617>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB connector, nominal cross section: 6 mm<sup>2</sup>, color: green, nominal current: 41 A, rated voltage (III/2): 1000 V, contact surface: Ag, contact connection type: Socket, number of potentials: 6, number of rows: 1, number of positions: 6, number of connections: 6, product range: PC 6/..-STF, pitch: 10.16 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON PC 16, locking: Screw locking mechanism, mounting method: Screw flange, type of packaging: packed in cardboard

## Your advantages

- Well-known connection principle allows worldwide use
- Low temperature rise, thanks to maximum contact force
- Allows connection of two conductors
- Integrated double steel spring provides additional safety in the event of temperature and power fluctuations
- Screwable flange for superior mechanical stability
- Integrated protective guide prevents incorrect insertion of the conductor underneath the tension sleeve

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1913617       |
| Packing unit                         | 25 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | AA04          |
| Product key                          | AADADB        |
| GTIN                                 | 4017918179090 |
| Weight per piece (including packing) | 54.42 g       |
| Weight per piece (excluding packing) | 52.068 g      |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

# PC 6/ 6-STF-10,16 - PCB connector

1913617

<https://www.phoenixcontact.com/us/products/1913617>



## Technical data

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | PCB connector         |
| Product family        | PC 6/..-STF           |
| Product line          | COMBICON Connectors L |
| Type                  | Standard              |
| Number of positions   | 6                     |
| Pitch                 | 10.16 mm              |
| Number of connections | 6                     |
| Number of rows        | 1                     |
| Number of potentials  | 6                     |
| Mounting flange       | Screw flange          |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 41 A   |
| Nominal voltage $U_N$       | 1000 V |
| Rated voltage (III/3)       | 1000 V |
| Rated surge voltage (III/3) | 8 kV   |
| Rated voltage (III/2)       | 1000 V |
| Rated surge voltage (III/2) | 8 kV   |
| Rated voltage (II/2)        | 1000 V |
| Rated surge voltage (II/2)  | 6 kV   |

### Connection data

#### Connection technology

|                         |                   |
|-------------------------|-------------------|
| Type                    | Standard          |
| Connector system        | COMBICON PC 16    |
| Nominal cross section   | 6 mm <sup>2</sup> |
| Contact connection type | Socket            |

#### Interlock

|                   |                         |
|-------------------|-------------------------|
| Locking type      | Screw locking mechanism |
| Mounting flange   | Screw flange            |
| Tightening torque | 0.3 Nm ... 0.7 Nm       |

#### Conductor connection

|                                    |   |
|------------------------------------|---|
| Connection method                  | Screw connection with tension sleeve        |
| Conductor/PCB connection direction | 0 °   |
| Conductor cross section rigid      | 0.75 mm <sup>2</sup> ... 10 mm <sup>2</sup> |
| Conductor cross section flexible   | 0.75 mm <sup>2</sup> ... 6 mm <sup>2</sup>  |
| Conductor cross section AWG        | 18 ... 8                                    |

# PC 6/ 6-STF-10,16 - PCB connector

1913617

<https://www.phoenixcontact.com/us/products/1913617>



|   |   |
|---|---|
| Conductor cross section flexible, with ferrule without plastic sleeve                     | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Conductor cross section, flexible, with ferrule, with plastic sleeve                      | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| 2 conductors with same cross section, solid   | 0.75 mm <sup>2</sup> ... 4 mm <sup>2</sup>  |
| 2 conductors with same cross section, flexible  | 0.75 mm <sup>2</sup> ... 6 mm <sup>2</sup>  |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Stripping length  | 12 mm                                       |
| Drive form screw head   | Slotted (L)                                 |
| Tightening torque   | 1.2 Nm ... 1.5 Nm                           |

## Material specifications

### Material data - contact

|  |  |
|--|--|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy   |
| Surface characteristics                  | Selective coating  |
| Metal surface terminal point (top layer) | Silver (4 - 8 µm Ag)   |
| Metal surface contact area (top layer)   | Silver (4 - 8 µm Ag)   |

### Material data - housing

|   |              |
|---|--------------|
| Color (Housing)   | green (6021) |
| Insulating material   | PA           |
| Insulating material group   | I            |
| CTI according to IEC 60112  | 600          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Dimensions

|                     |          |
|---------------------|----------|
| Dimensional drawing |          |
| Pitch               | 10.16 mm |
| Width [w]           | 78.72 mm |
| Height [h]          | 27.55 mm |
| Length [l]          | 39 mm    |

# PC 6/ 6-STF-10,16 - PCB connector

1913617

<https://www.phoenixcontact.com/us/products/1913617>



## Mounting

### Flange

|                   |                   |
|-------------------|-------------------|
| Tightening torque | 0.3 Nm ... 0.7 Nm |
|-------------------|-------------------|

## Notes

|                    |  |
|--------------------|--|
| Notes on operation | In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load. |
|--------------------|--|

## Environmental and real-life conditions

### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Electrical tests

### Air clearances and creepage distances |

|  |                     |
|--|---------------------|
| Specification  | IEC 60664-1:2007-04 |
| Insulating material group                              | I                   |
| Comparative tracking index (IEC 60112)                 | CTI 600             |
| Rated insulation voltage (III/3)                       | 1000 V              |
| Rated surge voltage (III/3)                            | 8 kV                |
| minimum clearance value - non-homogenous field (III/3) | 8 mm                |
| minimum creepage distance (III/3)                      | 12.5 mm             |
| Rated insulation voltage (III/2)                       | 1000 V              |
| Rated surge voltage (III/2)                            | 8 kV                |
| minimum clearance value - non-homogenous field (III/2) | 8 mm                |
| minimum creepage distance (III/2)                      | 8 mm                |
| Rated insulation voltage (II/2)                        | 1000 V              |
| Rated surge voltage (II/2)                             | 6 kV                |
| minimum clearance value - non-homogenous field (II/2)  | 5.5 mm              |
| minimum creepage distance (II/2)                       | 5.5 mm              |

## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|

# PC 6/ 6-STF-10,16 - PCB connector


1913617

<https://www.phoenixcontact.com/us/products/1913617>




## Drawings

Dimensional drawing



Diagram



Derating curve for: PC 6/..-STF-10,16 with PC 6-16/..-G1-10,16


# PC 6/ 6-STF-10,16 - PCB connector

1913617

<https://www.phoenixcontact.com/us/products/1913617>



Diagram



Derating curve for: PC 6/..-STF-10,16 with PCV 6-16/..-G1-10,16

# PC 6/ 6-STF-10,16 - PCB connector

1913617

<https://www.phoenixcontact.com/us/products/1913617>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1913617>

| cULus Recognized             |                       |                       |                   |                      |
|------------------------------|-----------------------|-----------------------|-------------------|----------------------|
| Approval ID: E60425-20010727 |                       |                       |                   |                      |
|                              | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| Use group B                  | 600 V                 | 50 A                  | 20 - 8            | -                    |
| Use group C                  | 600 V                 | 50 A                  | 20 - 8            | -                    |

# PC 6/ 6-STF-10,16 - PCB connector

1913617

<https://www.phoenixcontact.com/us/products/1913617>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460202 |
| ECLASS-15.0 | 27460202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002638 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PC 6/ 6-STF-10,16 - PCB connector

1913617

<https://www.phoenixcontact.com/us/products/1913617>



## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)