




Part Number : [5013280222](#)
Product Description : 3.30mm Pitch Wire-to-Wire
Inertia Lock Receptacle Housing, Single Row, 2 Circuits,
Red
Series Number : 501328
Status : Obsolete
Product Category : Connector Housings



Documents and Resources

Specifications

[5013289200-200.pdf](#)
[PS-501328-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	501328
Description	3.30mm Pitch Wire-to-Wire Inertia Lock Receptacle Housing, Single Row, 2 Circuits, Red
Application	Signal, Wire-to-Wire
Product Name	Inertia Lock
UPC	822348797011

Physical

Circuits (maximum)	2
Color - Resin	Red
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-25° to +80°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
-------------	-------------

3.30mm Pitch Wire-to-Wire Inertia Lock Plug Housing, Single Row, 2 Circuits, Red	<u>5013290222</u>
3.30mm Pitch Male Crimp Terminals	<u>56265</u>
3.30mm Pitch Male Crimp Terminals	<u>56279</u>

Use with Part(s)

Description	Part Number
3.30mm Pitch Wire-to-Wire Terminal Position Assurance (TPA) Retainer, 2 Circuits	<u>513480213</u>
Pico-Clasp Female Crimp Terminals	<u>501395</u>
3.30mm Pitch Female Crimp Terminals	<u>500989</u>

This document was generated on Apr 30, 2026