



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS		ELECTRICAL DATA		THIRD ANGLE PROJECTION	
OPERATING FORCE	6-12 LB	CONTACT ARRANGEMENT 4X S P D T		SCALE	NONE
FULL OVERTRAVEL FORCE	30 LB MAX	LOAD SEA LEVEL		DO NOT SCALE PRINT UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE	4 LB MIN	28 VDC		ONE PLACE	(.0) ± .030
PRETRAVEL	.040 MAX	LOAD 50,000 FT		TWO PLACE	(.00) ± .015
DIFFERENTIAL TRAVEL	.020 MAX	RES	7	THREE PLACE	(.000) ± .005
OVERTRAVEL	.250 MIN	IND	4	ANGLES	±
FREE POSITION		MOTOR	4	WEIGHT	

ANSI Y14.5M-1982 APPLIES

NOTES

- CORROSION RESISTANT STEEL ENCLOSURE
- SWITCH SEALED PER MIL-PRF-8805, SYMBOL 4
- IN ADDITION TO STANDARD MARKING, CUSTOMER PART NUMBER AND CURRENT CUSTOMER DRAWING REVISION LEVEL IS MARKED ON THE SWITCH NAME PLATE IF APPLICABLE
- COINCIDENCE OF OPERATION AND RELEASING POINTS: .010 OF PLUNGER TRAVEL HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
- GOLD PLATED SILVER CONTACT BASIC SWITCHES WELD SEAMS TO BE PAINTED TO RESIST CORROSION

5

7