Part Number : 2121950018
Product Description : Sentrality 3.40mm Top-entry, Height Above Board 5.17mm, Surface Mount Socket Assembly with +/-1.00mm Misalignment Capability, Tape and Reel
Series Number : 212195
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2121950018_sd.pdf

2121950018-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2043130018-PS-000.pdf

2043130018-TS-000.pdf

2043131234-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	212195
Description	Sentrality 3.40mm Top-entry, Height Above Board 5.17mm, Surface Mount Socket Assembly with +/-1.00mm Misalignment Capability, Tape and Reel
Application	Board-to-Board, Busbar-to-Board, Busbar-to-Busbar
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Receptacle
Product Name	Sentrality
UPC	191130978731

Agency

CSA	LR19980
UL	E29179

Downloaded from Arrow.com.

Electrical

Current - Maximum per Contact	75.0A
Voltage - Maximum	600V

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	3.40mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Height Above Board	5.17mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Top-entry
Net Weight	4.794/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Retention	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	600
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	205

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality Pins	203263
Sentrality 3.40mm Right-Angle Pins	204314

Downloaded from Arrow.com.