



Part Number : [349674021](#)

Product Description : Mini50 Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option A, Terminal Position 2 Plugged, Black

Series Number : 34967

Status : Active

Product Category : Connector Housings

---

## Documents & Resources

### Drawings

[Drawing 349674021\\_sd.pdf](#)

[Packaging Design Drawing PK-31301-898-000.pdf](#)

[Packaging Design Drawing PK-31301-898-001.pdf](#)

[Packaging Design Drawing PK-31301-898-001.pdf](#)

### 3D Models and Design Files

[3D Model 349674021\\_stp.zip](#)

### Specifications

[Application Specification AS-34894-0001-001.pdf](#)


[Product Specification 349670001-000.pdf](#)

[Test Summary 349670001-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	34967
Description	Mini50 Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option A, Terminal Position 2 Plugged, Black
Application	Automotive, Power, Sealed, Wire-to-Board
Comments	-40°C to +105°C operating temperature for tin terminals; -40°C to +125°C operating temperature for silver terminals
Product Family	Mini50 Connection Systems
Product Name	Mini50 Sealed
UPC	889056803656

### Physical

Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	3.310/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarization	A
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +125°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mates With	Molex does not manufacture the mating header interface. To provide you with maximum design flexibility, we include the interface specification drawing with the part drawing, and a 3D model is available at the following URL so that you may design the interface into your device as you require: COMING SOON

### Use with Part(s)

Description	Part Number
CTX50 Sealed Receptacle Terminals	<u>34905</u>

---

This document was generated on Jul 29, 2024