



## 001-0001

### 2.4 GHz Dipole Antenna 2400-2500 MHz

TE Connectivity is unmatched in offering multiple pre-certified antenna options for wireless modules. Pairing with a pre-certified RF antenna saves both certification time and costs. Our flexible antenna solutions provide unmatched flexibility to help solve your real-world design challenges.

#### ELECTRICAL SPECIFICATION

Operating Frequency (MHz)	2400-2500
VSWR - Max	≤2.5:1
Peak Gain (dBi)	+2.0 dBi
Nominal Impedance (Ohms)	50
Polarization	Linear vertical

#### MECHANICAL SPECIFICATION

Dimensions - mm (inches)	105 x 10 (4.13 x 0.39)
Weight - g (lbs.)	13 (0.46)
Antenna Color	Black


#### ENVIRONMENTAL SPECIFICATION

Operating Temperature - °C (°F)	-20 to +65°C (-4 to +149°F)
UL Rating	UL 94HB
Ingress Protection Rating	IP67

## CONFIGURATION

PART NUMBER	DESCRIPTION
001-0001	2.4 GHz dipole antenna for reverse polarity SMA connector
080-0001	U.FL to reverse polarity SMA cable, 105 mm

MECHANICAL DRAWING



TYPICAL ANTENNA REFLECTION PERFORMANCE




FIGURE 1: REFLECTION PARAMETERS FOR EXTENDED CONFIGURATION (S11)






FIGURE 2: REFLECTION PARAMETERS FOR FOLDED CONFIGURATION (S11)

## RADIATION PATTERNS


### Antenna Straight 2405 MHz




### Antenna Straight 2440 MHz




### Antenna Straight 2480 MHz




## Antenna Bent 2405



## Antenna Bent 2440 MHz



## Antenna Bent 2480



### TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

### te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original