




PRODUCT NUMBER	PITCH
ELxx11x200J0G	3.50 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item ① Male contact pin: Copper, Tin plated.
- Item ② Terminal (housing): Thermoplastic (UL 94 V-0)

Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5Sec
- Safety Approval: 

DIMENSION

Dim L	N×3.50
Dim B	(N-1)×3.50

N= Number of poles

Poles	Tolerance
2p-6p	±0.15
7p-12p	±0.20
13p-18p	±0.25
19p-24p	±0.30

PART NO.: EL xx 11 x 2 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
0	2	Black (RAL9005)	
02	2	Red (RAL3001/D)	
03	3	Orange (RAL2011/P)	
4	4	Yellow (RAL1018/A)	
5	5	Green (RAL6018/T)	
6	6	Blue (RAL5015/A)	
8	8	Grey (RAL7035/D)	
9	9	White (RAL1102)	
C	24	Green (RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family	
				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK	
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title	
					angles	X±0.5	TERMINAL BLOCK	
					flat	X.X±0.3	PLUGGABLE SOCKET, OPEN VERTICAL, DIP TYPE	
					X°±1°	X.XX±0.1	scale	
					dr	EVIN ZHONG 042214	dwg no	
					enr	EVIN ZHONG 042214	sheet 1 of 1 size	
					chr	HANKE FENG 042214	ELxx11x200J0G	
					appd	SHI JUN 042214	type	
							CUSTOMER Drawing	
sheet index	revision	A						
	sheet	1						