




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	08/06/13	
A		REVISED DIM.	7/9/15	HRTW



RECOMMENDED PCB LAYOUT [1.00]



SECTION X-X

SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Copper Alloy

Not: Copper Alloy, Tin plated

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 50V AC/DC

Current rating: 1A AC/DC

Contact resistance: 30 mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 500V AC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 15
A= .049 [1.25] x No. of Spaces + .177 [4.50]
B= .049 [1.25] x No. of Spaces
C= .049 [1.25] x No. of Spaces + .098 [2.50]
D= 2P: .083 [2.10], 3P: .134 [3.40], 4~5P: .183 [4.65]
6~9P: .262 [6.65], 10~15P: .339 [8.60]
E= 2P: .030 [0.75], 3P: .051 [1.30], 4~5P: .083 [2.10]
6~9P: .157 [4.00], 10~15P: .236 [6.00]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
STRAIGHT TYPE
125SH-K-XX-TS-SMT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
				.X				.X			
				.XX				.XX			
				.XXX				.XXX			
APPROVALS				DATE				DATE			
DRAWN				TW				08/06/13			
CHECKED				AL				08/06/13			
APPROVED											
SIZE				PART NO.				REV.			
X				125SH-K-XX-TS-SMT				A			
REF: S00124T				SCALE: NTS				SHEET 1 OF 1			