Part Number : 1200878480
Product Description : Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 4 Poles, Female (90°) to Male (Straight), 0.25mm² PVC Cable, 2.0m (6.56') Length
Series Number : 120087
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 484031E02M020



Documents and Resources

Drawings

1200878480_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 4 Poles, Female (90°) to Male (Straight), 0.25mm² PVC Cable, 2.0m (6.56') Length
IP Rating	IP68
Product Name	Micro-Change (M12),Nano-Change (M8)
Protocol	N/A
Type	Double Ended
UPC	78172532436

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	N/A
Cable Length	2.0m (6.56')

Downloaded from Arrow.com.

Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	None
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-30° TO +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	N/A

Downloaded from Arrow.com.