

- NOTES:
1. CARRIER MATL: COPPER ALLOY, 0.30 MM THICKNESS;
 2. FINISHED: REFER TO P/N SYSTEM;
 3. UNLESS OTHERWISE SPECIFIED, ALL INNER RADII ARE R0.10mm;
 4. DIMENSIONING SHALL BE INTERPRETED PER ASME Y14.5-2009;
 5. PACKING: 5KPCS/REEL, REF TO SPEC. GS-14-2813;
 6. APPLICABLE HOUSING: 10162695 SERIES;
 7. APPLICATION SPEC.: GS-20-0703;
 8. PART NUMBER CODE:
101162697-X0XLF




APPLICABLE WIRES:
2:AWG #18~20

RESERVE NUMBER


PLATING SPEC:
0: 5u" MIN. Au ON CONTACT AREA
Gold flash ON CRIMPING AREA

PITCH=11.00


REELING DIRECTION AFTER PLATING




SECTION E-E



SECTION C-C
SCALE 8:1



SECTION B-B
SCALE 8:1

10162697-X02LF		2.65	2.34	3.50	3.56	AWG #18~20	
PART NO.		DIM.A	DIM.B	DIM.C	DIM.D	APPLICABLE WIRES	
2021/09/22	projection 	mm 			size	scale	
2022/05/20					A3	N/A	
-					ecn no	ELX-N-44775-1	
2022/05/25	product family				-	rel level	Released
c Power Terminal				dwg no	10162697C		rev
boLock WTB connector							C
-		Product - Customer Drw				sheet 1 of 1	