



Color: ■ light gray



| Technical data     |                        |
|--------------------|------------------------|
| Number of spacings | 10 -times              |
| Electrical data    |                        |
| Rated current      | 32 A                   |
| Physical data      |                        |
| Width              | 60.1 mm / 2.366 inches |
| Height             | 4.1 mm / 0.161 inches  |
| Depth              | 19 mm / 0.748 inches   |

| Material data |            |
|---------------|------------|
| Color         | light gray |
| Fire load     | 0.034 MJ   |
| Weight        | 7.5 g      |

| Commercial data       |               |
|-----------------------|---------------|
| Product Group         | 22 (TOPJOB S) |
| PU (SPU)              | 25 pcs        |
| Packaging type        | Bag           |
| Country of origin     | DE            |
| GTIN                  | 4055143700634 |
| Customs tariff number | 85366990990   |

| Product Classification |                      |
|------------------------|----------------------|
| UNSPSC                 | 39121421             |
| eCl@ss 10.0            | 27-14-11-40          |
| eCl@ss 9.0             | 27-14-11-40          |
| ETIM 9.0               | EC000489             |
| ETIM 10.0              | EC000489             |
| ECCN                   | NO US CLASSIFICATION |

| Environmental Product Compliance |                         |
|----------------------------------|-------------------------|
| RoHS Compliance Status           | Compliant, No Exemption |

| Environmental requirements                                                                          |                                                    |                                                                       |                                                     |
|-----------------------------------------------------------------------------------------------------|----------------------------------------------------|-----------------------------------------------------------------------|-----------------------------------------------------|
| Environmental Testing                                                                               |                                                    | Environmental Testing                                                 |                                                     |
| Test specification:<br>Railway applications –<br>Rolling stock –<br>Electronic equipment            | DIN EN 50155 (VDE 0115-200):2022-06                | Shock test                                                            | Test passed according to Section 10 of the standard |
| Test procedure:<br>Railway applications –<br>Rolling stock equipment –<br>Vibration and shock tests | DIN EN 61373 (VDE 0115-0106):2011-04               | Shock pulse form                                                      | Half sine                                           |
| Spectrum/Mounting location                                                                          | Service life test, Category 1, Class A/B           | Acceleration                                                          | 5g (highest test level used for all axes)           |
| Functional test with noise-like oscillations                                                        | Test passed according to Section 8 of the standard | Shock duration                                                        | 30 ms                                               |
| Frequency                                                                                           | f <sub>1</sub> = 5 Hz to f <sub>2</sub> = 150 Hz   | Number of shocks (per axis)                                           | 3 pos. und 3 neg.                                   |
| Acceleration                                                                                        | 0.101g (highest test level used for all axes)      | Test directions                                                       | X, Y and Z axes                                     |
| Test duration per axis                                                                              | 10 min.                                            | Extended testing: Monitoring of contact faults and interruptions      | Passed                                              |
| Test directions                                                                                     | X, Y and Z axes                                    | Extended testing: Voltage drop measurement before and after each axis | Passed                                              |
| Monitoring of contact faults and interruptions                                                      | Passed                                             | Vibration and shock stress for rolling stock equipment                | Passed                                              |
| Voltage drop measurement before and after each axis                                                 | Passed                                             |                                                                       |                                                     |
| Simulated service life test through increased levels of noise-like oscillations                     | Test passed according to Section 9 of the standard |                                                                       |                                                     |
| Frequency                                                                                           | f <sub>1</sub> = 5 Hz to f <sub>2</sub> = 150 Hz   |                                                                       |                                                     |
| Acceleration                                                                                        | 0.572g (highest test level used for all axes)      |                                                                       |                                                     |
| Test duration per axis                                                                              | 5 h                                                |                                                                       |                                                     |
| Test directions                                                                                     | X, Y and Z axes                                    |                                                                       |                                                     |
| Extended testing: Monitoring of contact faults and interruptions                                    | Passed                                             |                                                                       |                                                     |
| Extended testing: Voltage drop measurement before and after each axis                               | Passed                                             |                                                                       |                                                     |

Approvals / Certificates

Declarations of conformity and manufacturer's declarations



| Approval                      | Standard | Certificate Name |
|-------------------------------|----------|------------------|
| Railway<br>WAGO GmbH & Co. KG | -        | Railway Ready    |

Downloads

Environmental Product Compliance

| Compliance Search                            |
|----------------------------------------------|
| Environmental Product<br>Compliance 2004-410 |



Documentation

| Bid Text |            |                 |                                                                                     |
|----------|------------|-----------------|-------------------------------------------------------------------------------------|
| 2004-410 | 19.02.2019 | xml<br>2.52 KB  |   |
| 2004-410 | 28.04.2017 | doc<br>23.50 KB |  |

CAD/CAE-Data

| CAD data              |
|-----------------------|
| 2D/3D Models 2004-410 |





| CAE data                      |
|-------------------------------|
| EPLAN Data Portal<br>2004-410 |
| WSCAD Universe<br>2004-410    |
| ZUKEN Portal 2004-410         |



Installation Notes

Commoning



Insert push-in type jumper bar and push down until it hits backstop.

**Removing a push-in type jumper bar:**  
Insert the operating tool between the jumper and partition wall of the dual jumper slots, then lift up the jumper.  
Place the operating tool in the center of jumpers for up to five contacts (see above), or alternately on both sides for jumpers with more than five contacts.


Commoning



Custom jumpers are created by breaking and removing jumper contacts (2000, 2001, 2002, 2004 Series).

Marking with a felt-tip pen.

Commoning



Stepping down via push-in type jumper bar.

**Stepping down via push-in type jumper bar:**  
Commoning via closed terminal side with end plate allows jumpering over two cross-section sizes, e.g., from 16 mm<sup>2</sup> (6 AWG) to 6 mm<sup>2</sup> (10 AWG) or from 6 mm<sup>2</sup> (10 AWG) to 2.5 mm<sup>2</sup> (14 AWG) (see illustration above).

**Stepping down via push-in type jumper bar:**  
Commoning via open terminal side with end plate allows jumpering over two cross-section sizes for 16 mm<sup>2</sup> (6 AWG) and 10 mm<sup>2</sup> (8 AWG) and one cross-section size for 6/4/2.5 mm<sup>2</sup> (10/12/14 AWG). An example: from 16 mm<sup>2</sup> (6 AWG) to 6 mm<sup>2</sup> (10 AWG) (see illustration above) or from 10 mm<sup>2</sup> (8 AWG) to 4 mm<sup>2</sup> (12 AWG).

**Note:**  
The total current of the outgoing circuits must not exceed the nominal current of the step-down jumper/push-in type jumper bar.