

COAXIAL CONNECTOR, N, 50 Ohm, Right angle cable plug (male)

16_N-50-4-53/199_NE

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration		
Interface type	Gender	Standard
N	plug	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data	
Weight	0.0392 kg
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, N, 50 Ohm, Right angle cable plug (male)

16_N-50-4-53/199_NE

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22645021	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22645021	16_N-50-4-53/199_NE	Single

Suitable cables	
Cable group	X9 - 4 mm / 50 Ohm S16 - 4 mm / 50 Ohm
Suitable cables	S_04272_B

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543189	76_Z-0-4-1	Crimping dies
22646290	74_Z-0-0-264	Trimming tool

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3086 / Date of publication: 11.07.2025 / uncontrolled copy