


PCB Layout



Technical data

- 1.Nominal voltage: 300V/20A
PITCH: 8.25mm
- 2.Connection capacity:
AWG 22-12
- 3.Insulation Withstanding Voltage:
AC 2500V/MIN
- 4.Insulation Resistance:
1000MΩ or more at DC500V
- 5.Tightening torque:
10.15kgf.cm (8.8 Lb-In / 1.0N.m)
- 6.Screw thread: M3
- 7.Operating temperature range:-40°C ~ 115°C
Soldering temperature:250°C±10°C /5s
- 8.Undimensioned Tolerances:

Dim.L=Px8.25+1.95 Dim.B=(P-1)x8.25 P= number of poles		
0-30mm	±0.15	±0.20
over 30mm-60mm	±0.20	±0.30
over 60mm-90mm	±0.25	±0.40
over 90mm-180mm	±0.30	±0.50
over 180mm	±0.50	±0.80

- 9.Safety approval:
- 10.RoHS Compliance

Part No.: OSTYK331XX030

No. of Poles
02 2 Poles
03 3 Poles
...
24 24 Poles

3	SCREW+WASHER	STEEL	M3x0.5, Ni Plated	P
2	CONTACT	BRASS	M3x0.5, Tin PLATED	P
1	BODY	PA66 UL94V-0	Black	1
ITEM	NAME OF PART	MATERIAL	NOTES	Q"TY
DWG	WF. Zhang	DATE 2016.06.23	UNITS: MM	SHEET: 1 OF 1
CHK.	WF. Zhang	DATE 2016.09.09	SCALE: NONE 2:1 (:)	REV: A
APP.		DATE	TITLE: OSTYK331 8.25 Series	X. ±0.50
			Barrier Terminal block	X.X ±0.30
			PART NO. OSTYK331XX030	X° ±1°
			DWG NO. OSTYK331XX030.dwg	

SIGN	DESCRIPTION	CHK.	DATE



ON-SHORE TECHNOLOGY, INC.

