

Specifications



Eaton B0820-2R5225-R

Eaton B supercapacitor, 2.5 V, 2.2 F, 0.2 Ω , CYLINDRICAL

General specifications

PRODUCT NAME	Eaton B cylindrical cell supercapacitor
CATALOG NUMBER	B0820-2R5225-R
UPC	051712824361
EAN	5027590220316
PRODUCT HEIGHT	21 mm
PRODUCT DIAMETER	8.5 mm
PRODUCT WEIGHT	1.5 g
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Recognized

Product specifications

PACKING	Bulk
CONTACT CONFIGURATION	Vertical
SIZE	8 x 20 mm
TERMINALS	Through hole
SHAPE	Cylindrical
DC EQUIVALENT SERIES RESISTANCE (ESR)	0.2 Ω
OPERATING TEMPERATURE RANGE	-25 °C to +70 °C
SERIES	B
MAX VOLTAGE	2.5 V
CAPACITANCE	2.2 F
LEAKAGE	9 μ A
THERMAL RESISTANCE	76 °C/W
ENERGY	6.9 J
POWER	3.8 W
PEAK CURRENT (1 SEC)	1.9 A
CONTINUOUS CURRENT (15 °C RISE)	1 A
CAPACITANCE END OF LIFE RATING	70%
ESR END OF LIFE RATING	300%
GRADE	Commercial

Resources

	Supercapacitor soldering guidelines
APPLICATION NOTES	High power supercapacitors enable new power applications and replace batteries
BROCHURES	Supercapacitor selection guide Eaton's electronics components portfolio overview brochure
MANUALS AND USER GUIDES	Methods for measuring capacitance, inflow current, internal resistance and ESR
PRODUCT NOTIFICATIONS	Logo and branding changes (PCN16044) Supercapacitors definition of the -R part number suffix change Supercapacitor lot code and date code change Shelf Life of supercapacitor products product notice (PCN15011m) Shipping box and external and internal label update
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - B0820-2R5225-R B Supercapacitor data sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

