




REV.	ECN NO.	MODIFY CONTENT	DATE
X	XXXXXX	NEW RELEASE	06/21/16



RECOMMENDED PCB LAYOUT
TOLERANCES: ±0.05

NOTES:

1.MATERIAL:

- 1.1 Housing: LCP E130i, UL94V-0, Color:Black
- 1.2 Terminal: C5191-H, 80u"Min matte tin plated on solder tails.
- 1.3 Stator: C5191-H
- 1.4 Shell: SUS201 1/2H.

2.SPECIALITY:


- 2.1 Rated Current:1.0A
- 2.2 Rated Voltage:30V
- 2.3 Contact Resistance:50m ohm Max
- 2.4 Insulation Resistance:100M ohm Min 100V DC
- 2.5 Dielectric Withstanding Voltage:100V AC
- 2.6 Solder Ability:245±5°C;5±0.5s
- 2.7 Durability:5000 cycles
- 2.8 Operating Condition:Temperature: -30°C~+80°C; Humidity:80%R.H Max
- 2.9 Solder Temperature:260°C;5s

3. Part Number: 10101514XX-0-2A

Packing by Reel

71: Contact area: Au 1u",

75: Contact area: Au 15u" Min, 50u" min. nickel under plated over all



PIN NO.	PIN ASSIGNMENT
PIN 8	DAT1
PIN 7	DAT0
PIN 6	VSS
PIN 5	GLK
PIN 4	VDD
PIN 3	CMD
PIN 2	CD/DAT3
PIN 1	DAT2

GENERAL TOLERANCE		FILE.NO.	10101514XX0XX	PART.NO.	10101514XX0XX	DRAWN	Leo.zeng	MATERIAL		SCALE	N/A
X.±0.50	x. °± 5 °	REV.	X	TITLE	T-FLASH CARD HINGED TYPE	CHECKED	Weison.lu	DATE	12.29/2016	UNIT	mm
.X±0.38	.x °± 2 °	SIZE		SHEET	1/1	APPROVED	Amphenol Shouhmin Industry				
.XX±0.25	.xx± 1 °	A4									

