





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-13-015151	16DEC2013	FL	FY



- NOTES:
- GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN.AND ACTION PIN: 0,5µm TIN MIN. FOR PLATING OF MATING SURFACES SEE PERFORMANCE LEVEL SHOWN IN PART NUMBER TABLE.
 - MATERIAL; PHOSPHORBRONZE.
 - ROW "f" 11 PLATED THROUGH HOLES FOR LOWERSHIELD.
 - HOLE PATTERN FOR FEMALE CONNECTOR TYPE B-22 COLUMNS WITH UPBERSHIELD, 110+11 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
 - MAX. BOARD THICKNESS 3,5 mm.
 - SHIELDS LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REF: TR-NWT-001217 ISSUE 1, SEPT. 1992.
 - CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
 - CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
 - CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III,CENTRAL OFFICE APPLICATIONS.
 - 0.76µm MIN GOLD PLATING AT MATING SURFACE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. Mooij	08-JUL-05	TE Connectivity	
DIMENSIONS: mm		CHK B. Mooij	08-JUL-05		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. Broeksteeg	08-JUL-05	NAME Z-PACK 2mm HM GROUND RETURN LOWERSHIELD TYPE B-22 COLUMNS	
	0-PLC ± -	PRODUCT SPEC	108-19082		
	1-PLC ± -	APPLICATION SPEC	114-19029		
	2-PLC ± -				
MATERIAL		WEIGHT	-	SIZE A2	CAGE CODE 00779
		FINISH	-	DRAWING NO C=5352468	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 of 1	REV C