




Part Number : [638084800](#)

Product Description : FA2 Mechanical Feed Crimp
Applicator for CTX50 Unsealed Receptacle Terminal,
0.22mm² and 24 AWG Wires

Series Number : 207127

Status : Active

Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

[638084800-000.pdf](#)

[TM-638000029-001.pdf](#)

[638080200-000.pdf](#)

[638080200ES-000.pdf](#)

[638080200CN-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FA2 Mechanical Feed Crimp Applicator for CTX50 Unsealed Receptacle Terminal, 0.22mm ² and 24 AWG Wires
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	CTX50,FA2
Tool Type	Applicator
UPC	191128914376
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than

	Molex Tooling is used or where Molex Tooling is modified.
--	---

Physical

Net Weight	1.000/g
------------	---------

Mates With / Use With

Use with Part(s)

Description	Part Number
TM-2000 Universal Press	<u>638008300</u>
TM-2000 Universal Press (Europe 220V)	<u>638008400</u>
TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG	<u>638017200</u>
TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG	<u>638017300</u>
TM-4000 Universal Crimp Press, 240AC 50/60Hz, Used for product up to 4 AWG	<u>638017600</u>
Use With	Most Industry Standard Presses or Wire Process Machines

Applicable Parts

Description	Part Number
CTX50 Receptacle Terminal, Unsealed, Tin Plating, M-Grip, D-Wind, Left Payoff	<u>5600230421</u>
CTX50 Receptacle Terminal, Unsealed, Tin Plating, M-Grip, D-Wind, Left Payoff	<u>5600230721</u>

This document was generated on Jan 01, 2026