





HONEYWELL PART NUMBER
4SX17-T
PRODUCT CODE VDF0856

REV	DOCUMENT	CHANGED BY	CHECK
5	0038447	SS 28MAR08	BLR



- NOTE -
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA OF .188±.002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 400°F
 - 4 - JHN182 BRANDED ON SIDE OF SWITCH

RELEASE NO.	PR-4958
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 		DRAWN	VK	01MAR08	Honeywell			
OPERATING FORCE — — 5 OZ MAX		CONTACT ARRANGEMENT SPDT				CHECK	RJ	01MAR08				
RELEASE FORCE— — — — 1 OZ MIN		30 VDC 3 AMP RES 1.5 AMP IND.		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY	SIZE	TYPE	DRAWING NAME		REV	
DIFFERENTIAL TRAVEL— — — .003 MAX							B	I	4SX17-T		5	
OVERTRAVEL — — — — — .006 MIN						SCALE	-	WEIGHT .003 LB MAX	SHEET 1 OF 1			