




## M74HC573

### OCTAL D-TYPE LATCH WITH 3 STATE OUTPUT NON INVERTING

- HIGH SPEED:  
 $t_{PD} = 13ns$  (TYP.) at  $V_{CC} = 6V$
- LOW POWER DISSIPATION:  
 $I_{CC} = 4\mu A$  (MAX.) at  $T_A = 25^\circ C$
- HIGH NOISE IMMUNITY:  
 $V_{NIH} = V_{NIL} = 28\% V_{CC}$  (MIN.)
- SYMMETRICAL OUTPUT IMPEDANCE:  
 $|I_{OH}| = I_{OL} = 6mA$  (MIN.)
- BALANCED PROPAGATION DELAYS:  
 $t_{PLH} \approx t_{PHL}$
- WIDE OPERATING VOLTAGE RANGE:  
 $V_{CC}$  (OPR) = 2V to 6V
- PIN AND FUNCTION COMPATIBLE WITH  
74 SERIES 573



#### ORDER CODES

| PACKAGE | TUBE        | T & R          |
|---------|-------------|----------------|
| DIP     | M74HC573B1R |                |
| SOP     | M74HC573M1R | M74HC573RM13TR |
| TSSOP   |             | M74HC573TTR    |

#### DESCRIPTION

The M74HC573 is an high speed CMOS OCTAL LATCH WITH 3-STATE OUTPUTS fabricated with silicon gate C<sup>2</sup>MOS technology.

This 8-BIT D-Type latches is controlled by a latch enable input (LE) and output enable input (OE).


While the LE input is held at a high level, the Q outputs will follow the data input precisely. When LE is taken low, the Q outputs will be latched precisely at the logic level of D input data.

While the  $\overline{OE}$  input is at low level, the eight outputs will be in a normal logic state (high or low logic level) and while is at high level the outputs will be in a high impedance state.


The 3-State output configuration and the wide choice of outline make bus organized system simple.

All inputs are equipped with protection circuits against static discharge and transient excess voltage.

#### PIN CONNECTION AND IEC LOGIC SYMBOLS



INPUT AND OUTPUT EQUIVALENT CIRCUIT



PIN DESCRIPTION


| PIN No                         | SYMBOL          | NAME AND FUNCTION                        |
|--------------------------------|-----------------|------------------------------------------|
| 1                              | $\overline{OE}$ | 3 State Output Enable Input (Active LOW) |
| 2, 3, 4, 5, 6, 7, 8, 9         | D0 to D7        | Data Inputs                              |
| 12, 13, 14, 15, 16, 17, 18, 19 | Q0 to Q7        | 3 State Latch Outputs                    |
| 11                             | LE              | Latch Enable Input                       |
| 10                             | GND             | Ground (0V)                              |
| 20                             | V <sub>CC</sub> | Positive Supply Voltage                  |

TRUTH TABLE

| INPUTS          |    |   | OUTPUTS       |
|-----------------|----|---|---------------|
| $\overline{OE}$ | LE | D | Q             |
| H               | X  | X | Z             |
| L               | L  | X | NO CHANGE (*) |
| L               | H  | L | L             |
| L               | H  | H | H             |

X: Don't Care  
Z: High Impedance  
(\*): Q Outputs are latched at the time when the LE input is taken low logic level.

LOGIC DIAGRAM



**ABSOLUTE MAXIMUM RATINGS**

| Symbol                | Parameter                     | Value                  | Unit |
|-----------------------|-------------------------------|------------------------|------|
| $V_{CC}$              | Supply Voltage                | -0.5 to +7             | V    |
| $V_I$                 | DC Input Voltage              | -0.5 to $V_{CC} + 0.5$ | V    |
| $V_O$                 | DC Output Voltage             | -0.5 to $V_{CC} + 0.5$ | V    |
| $I_{IK}$              | DC Input Diode Current        | $\pm 20$               | mA   |
| $I_{OK}$              | DC Output Diode Current       | $\pm 20$               | mA   |
| $I_O$                 | DC Output Current             | $\pm 35$               | mA   |
| $I_{CC}$ or $I_{GND}$ | DC $V_{CC}$ or Ground Current | $\pm 70$               | mA   |
| $P_D$                 | Power Dissipation             | 500(*)                 | mW   |
| $T_{stg}$             | Storage Temperature           | -65 to +150            | °C   |
| $T_L$                 | Lead Temperature (10 sec)     | 300                    | °C   |

Absolute Maximum Ratings are those values beyond which damage to the device may occur. Functional operation under these conditions is not implied.

(\*) 500mW at 65 °C; derate to 300mW by 10mW/°C from 65°C to 85°C

**RECOMMENDED OPERATING CONDITIONS**

| Symbol                          | Parameter                |                        | Value                | Unit |
|---------------------------------|--------------------------|------------------------|----------------------|------|
| V <sub>CC</sub>                 | Supply Voltage           |                        | 2 to 6               | V    |
| V <sub>I</sub>                  | Input Voltage            |                        | 0 to V <sub>CC</sub> | V    |
| V <sub>O</sub>                  | Output Voltage           |                        | 0 to V <sub>CC</sub> | V    |
| T <sub>op</sub>                 | Operating Temperature    |                        | -55 to 125           | °C   |
| t <sub>r</sub> , t <sub>f</sub> | Input Rise and Fall Time | V <sub>CC</sub> = 2.0V | 0 to 1000            | ns   |
|                                 |                          | V <sub>CC</sub> = 4.5V | 0 to 500             | ns   |
|                                 |                          | V <sub>CC</sub> = 6.0V | 0 to 400             | ns   |

## DC SPECIFICATIONS

| Symbol          | Parameter                             | Test Condition         |                                                                                                | Value                 |      |       |             |      |              |      | Unit |  |
|-----------------|---------------------------------------|------------------------|------------------------------------------------------------------------------------------------|-----------------------|------|-------|-------------|------|--------------|------|------|--|
|                 |                                       | V <sub>CC</sub><br>(V) |                                                                                                | T <sub>A</sub> = 25°C |      |       | -40 to 85°C |      | -55 to 125°C |      |      |  |
|                 |                                       |                        |                                                                                                | Min.                  | Typ. | Max.  | Min.        | Max. | Min.         | Max. |      |  |
| V <sub>IH</sub> | High Level Input Voltage              | 2.0                    |                                                                                                | 1.5                   |      |       | 1.5         |      | 1.5          |      | V    |  |
|                 |                                       | 4.5                    |                                                                                                | 3.15                  |      |       | 3.15        |      | 3.15         |      |      |  |
|                 |                                       | 6.0                    |                                                                                                | 4.2                   |      |       | 4.2         |      | 4.2          |      |      |  |
| V <sub>IL</sub> | Low Level Input Voltage               | 2.0                    |                                                                                                |                       |      | 0.5   |             | 0.5  |              | 0.5  | V    |  |
|                 |                                       | 4.5                    |                                                                                                |                       |      | 1.35  |             | 1.35 |              | 1.35 |      |  |
|                 |                                       | 6.0                    |                                                                                                |                       |      | 1.8   |             | 1.8  |              | 1.8  |      |  |
| V <sub>OH</sub> | High Level Output Voltage             | 2.0                    | I <sub>O</sub> =-20 μA                                                                         | 1.9                   | 2.0  |       | 1.9         |      | 1.9          |      | V    |  |
|                 |                                       | 4.5                    | I <sub>O</sub> =-20 μA                                                                         | 4.4                   | 4.5  |       | 4.4         |      | 4.4          |      |      |  |
|                 |                                       | 6.0                    | I <sub>O</sub> =-20 μA                                                                         | 5.9                   | 6.0  |       | 5.9         |      | 5.9          |      |      |  |
|                 |                                       | 4.5                    | I <sub>O</sub> =-6.0 mA                                                                        | 4.18                  | 4.31 |       | 4.13        |      | 4.10         |      |      |  |
|                 |                                       | 6.0                    | I <sub>O</sub> =-7.8 mA                                                                        | 5.68                  | 5.8  |       | 5.63        |      | 5.60         |      |      |  |
| V <sub>OL</sub> | Low Level Output Voltage              | 2.0                    | I <sub>O</sub> =20 μA                                                                          |                       | 0.0  | 0.1   |             | 0.1  |              | 0.1  | V    |  |
|                 |                                       | 4.5                    | I <sub>O</sub> =20 μA                                                                          |                       | 0.0  | 0.1   |             | 0.1  |              | 0.1  |      |  |
|                 |                                       | 6.0                    | I <sub>O</sub> =20 μA                                                                          |                       | 0.0  | 0.1   |             | 0.1  |              | 0.1  |      |  |
|                 |                                       | 4.5                    | I <sub>O</sub> =6.0 mA                                                                         |                       | 0.17 | 0.26  |             | 0.33 |              | 0.40 |      |  |
|                 |                                       | 6.0                    | I <sub>O</sub> =7.8 mA                                                                         |                       | 0.18 | 0.26  |             | 0.33 |              | 0.40 |      |  |
| I <sub>I</sub>  | Input Leakage Current                 | 6.0                    | V <sub>I</sub> = V <sub>CC</sub> or GND                                                        |                       |      | ± 0.1 |             | ± 1  |              | ± 1  | μA   |  |
| I <sub>OZ</sub> | High Impedance Output Leakage Current | 6.0                    | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub><br>V <sub>O</sub> = V <sub>CC</sub> or GND |                       |      | ± 0.5 |             | ± 5  |              | ± 10 | μA   |  |
| I <sub>CC</sub> | Quiescent Supply Current              | 6.0                    | V <sub>I</sub> = V <sub>CC</sub> or GND                                                        |                       |      | 4     |             | 40   |              | 80   | μA   |  |

AC ELECTRICAL CHARACTERISTICS ( $C_L = 50 \text{ pF}$ , Input  $t_r = t_f = 6 \text{ ns}$ )


| Symbol                                 | Parameter                          | Test Condition         |                        |                       | Value                 |      |      |             |      |              |      | Unit |
|----------------------------------------|------------------------------------|------------------------|------------------------|-----------------------|-----------------------|------|------|-------------|------|--------------|------|------|
|                                        |                                    | V <sub>CC</sub><br>(V) | C <sub>L</sub><br>(pF) |                       | T <sub>A</sub> = 25°C |      |      | -40 to 85°C |      | -55 to 125°C |      |      |
|                                        |                                    |                        |                        |                       | Min.                  | Typ. | Max. | Min.        | Max. | Min.         | Max. |      |
| t <sub>TLH</sub> t <sub>THL</sub>      | Output Transition Time             | 2.0                    | 50                     |                       |                       | 25   | 60   |             | 75   |              | 90   | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 7    | 12   |             | 15   |              | 18   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 6    | 10   |             | 13   |              | 15   |      |
| t <sub>PLH</sub> t <sub>PHL</sub>      | Propagation Delay Time<br>(LE - Q) | 2.0                    | 50                     |                       |                       | 50   | 115  |             | 145  |              | 175  | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 15   | 23   |             | 29   |              | 35   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 13   | 20   |             | 25   |              | 30   |      |
|                                        |                                    | 2.0                    | 150                    |                       |                       | 60   | 155  |             | 195  |              | 235  | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 20   | 31   |             | 39   |              | 47   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 17   | 26   |             | 33   |              | 40   |      |
| t <sub>PLH</sub> t <sub>PHL</sub>      | Propagation Delay Time<br>(D - Q)  | 2.0                    | 50                     |                       |                       | 42   | 110  |             | 140  |              | 165  | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 14   | 22   |             | 28   |              | 33   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 12   | 19   |             | 24   |              | 28   |      |
|                                        |                                    | 2.0                    | 150                    |                       |                       | 57   | 150  |             | 190  |              | 225  | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 19   | 30   |             | 38   |              | 45   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 16   | 26   |             | 32   |              | 38   |      |
| t <sub>PZL</sub> t <sub>PZH</sub>      | High Impedance Output Enable Time  | 2.0                    | 50                     | R <sub>L</sub> = 1 KΩ |                       | 55   | 140  |             | 175  |              | 210  | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 17   | 28   |             | 35   |              | 42   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 14   | 24   |             | 30   |              | 36   |      |
|                                        |                                    | 2.0                    | 150                    | R <sub>L</sub> = 1 KΩ |                       | 66   | 180  |             | 225  |              | 270  | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 22   | 36   |             | 45   |              | 54   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 19   | 31   |             | 38   |              | 46   |      |
| t <sub>PLZ</sub> t <sub>PHZ</sub>      | High Impedance Output Disable Time | 2.0                    | 50                     | R <sub>L</sub> = 1 KΩ |                       | 40   | 125  |             | 155  |              | 190  | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 17   | 25   |             | 31   |              | 38   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 15   | 21   |             | 26   |              | 32   |      |
| t <sub>W(L)</sub><br>t <sub>W(H)</sub> | Minimum Pulse Width                | 2.0                    | 50                     |                       |                       | 40   | 75   |             | 95   |              | 110  | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 8    | 15   |             | 19   |              | 22   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 7    | 13   |             | 16   |              | 19   |      |
| t <sub>s</sub>                         | Minimum Set-up Time                | 2.0                    | 50                     |                       |                       | 16   | 50   |             | 65   |              | 75   | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       | 5    | 10   |             | 13   |              | 15   |      |
|                                        |                                    | 6.0                    |                        |                       |                       | 3    | 9    |             | 11   |              | 13   |      |
| t <sub>h</sub>                         | Minimum Hold Time                  | 2.0                    | 50                     |                       |                       |      | 5    |             | 5    |              | 5    | ns   |
|                                        |                                    | 4.5                    |                        |                       |                       |      | 5    |             | 5    |              | 5    |      |
|                                        |                                    | 6.0                    |                        |                       |                       |      | 5    |             | 5    |              | 5    |      |

CAPACITIVE CHARACTERISTICS

| Symbol           | Parameter                              | Test Condition         |  |  | Value                 |      |      |             |      |              | Unit |      |
|------------------|----------------------------------------|------------------------|--|--|-----------------------|------|------|-------------|------|--------------|------|------|
|                  |                                        | V <sub>CC</sub><br>(V) |  |  | T <sub>A</sub> = 25°C |      |      | -40 to 85°C |      | -55 to 125°C |      |      |
|                  |                                        |                        |  |  | Min.                  | Typ. | Max. | Min.        | Max. | Min.         |      | Max. |
| C <sub>IN</sub>  | Input Capacitance                      |                        |  |  |                       | 5    | 10   |             | 10   |              | 10   | pF   |
| C <sub>OUT</sub> | Output Capacitance                     |                        |  |  |                       | 10   |      |             |      |              |      | pF   |
| C <sub>PD</sub>  | Power Dissipation Capacitance (note 1) |                        |  |  |                       | 51   |      |             |      |              |      | pF   |

1) C<sub>PD</sub> is defined as the value of the IC's internal equivalent capacitance which is calculated from the operating current consumption without load. (Refer to Test Circuit). Average operating current can be obtained by the following equation: I<sub>CC(opr)</sub> = C<sub>PD</sub> × V<sub>CC</sub> × f<sub>IN</sub> + I<sub>CC</sub>/8 (per Flip Flop) and the C<sub>PD</sub> when n pcs of Flip Flop operate, can be gained by the following equation: C<sub>PD(TOTAL)</sub> = 33 + 18 × n (pF)


TEST CIRCUIT




| TEST                                | SWITCH          |
|-------------------------------------|-----------------|
| t <sub>PLH</sub> , t <sub>PHL</sub> | Open            |
| t <sub>PZL</sub> , t <sub>PLZ</sub> | V <sub>CC</sub> |
| t <sub>PZH</sub> , t <sub>PHZ</sub> | GND             |


C<sub>L</sub> = 50pF/150pF or equivalent (includes jig and probe capacitance)  
R<sub>1</sub> = 1KΩ or equivalent  
R<sub>T</sub> = Z<sub>OUT</sub> of pulse generator (typically 50Ω)

**WAVEFORM 1: LE TO Qn PROPAGATION DELAYS, LE MINIMUM PULSE WIDTH, Dn TO LE SETUP AND HOLD TIMES (f=1MHz; 50% duty cycle)**




**WAVEFORM 2: OUTPUT ENABLE AND DISABLE TIMES (f=1MHz; 50% duty cycle)**



**WAVEFORM 3: PROPAGATION DELAY TIMES** ( $f=1\text{MHz}$ ; 50% duty cycle)


## Plastic DIP-20 (0.25) MECHANICAL DATA

| DIM. | mm.   |       |      | inch  |       |       |
|------|-------|-------|------|-------|-------|-------|
|      | MIN.  | TYP   | MAX. | MIN.  | TYP.  | MAX.  |
| a1   | 0.254 |       |      | 0.010 |       |       |
| B    | 1.39  |       | 1.65 | 0.055 |       | 0.065 |
| b    |       | 0.45  |      |       | 0.018 |       |
| b1   |       | 0.25  |      |       | 0.010 |       |
| D    |       |       | 25.4 |       |       | 1.000 |
| E    |       | 8.5   |      |       | 0.335 |       |
| e    |       | 2.54  |      |       | 0.100 |       |
| e3   |       | 22.86 |      |       | 0.900 |       |
| F    |       |       | 7.1  |       |       | 0.280 |
| I    |       |       | 3.93 |       |       | 0.155 |
| L    |       | 3.3   |      |       | 0.130 |       |
| Z    |       |       | 1.34 |       |       | 0.053 |




SO-20 MECHANICAL DATA

| DIM. | mm.        |       |       | inch  |       |       |
|------|------------|-------|-------|-------|-------|-------|
|      | MIN.       | TYP   | MAX.  | MIN.  | TYP.  | MAX.  |
| A    |            |       | 2.65  |       |       | 0.104 |
| a1   | 0.1        |       | 0.2   | 0.004 |       | 0.008 |
| a2   |            |       | 2.45  |       |       | 0.096 |
| b    | 0.35       |       | 0.49  | 0.014 |       | 0.019 |
| b1   | 0.23       |       | 0.32  | 0.009 |       | 0.012 |
| C    |            | 0.5   |       |       | 0.020 |       |
| c1   | 45° (typ.) |       |       |       |       |       |
| D    | 12.60      |       | 13.00 | 0.496 |       | 0.512 |
| E    | 10.00      |       | 10.65 | 0.393 |       | 0.419 |
| e    |            | 1.27  |       |       | 0.050 |       |
| e3   |            | 11.43 |       |       | 0.450 |       |
| F    | 7.40       |       | 7.60  | 0.291 |       | 0.300 |
| L    | 0.50       |       | 1.27  | 0.020 |       | 0.050 |
| M    |            |       | 0.75  |       |       | 0.029 |
| S    | 8° (max.)  |       |       |       |       |       |



## TSSOP20 MECHANICAL DATA

| DIM. | mm.  |          |      | inch  |            |        |
|------|------|----------|------|-------|------------|--------|
|      | MIN. | TYP      | MAX. | MIN.  | TYP.       | MAX.   |
| A    |      |          | 1.2  |       |            | 0.047  |
| A1   | 0.05 |          | 0.15 | 0.002 | 0.004      | 0.006  |
| A2   | 0.8  | 1        | 1.05 | 0.031 | 0.039      | 0.041  |
| b    | 0.19 |          | 0.30 | 0.007 |            | 0.012  |
| c    | 0.09 |          | 0.20 | 0.004 |            | 0.0089 |
| D    | 6.4  | 6.5      | 6.6  | 0.252 | 0.256      | 0.260  |
| E    | 6.2  | 6.4      | 6.6  | 0.244 | 0.252      | 0.260  |
| E1   | 4.3  | 4.4      | 4.48 | 0.169 | 0.173      | 0.176  |
| e    |      | 0.65 BSC |      |       | 0.0256 BSC |        |
| K    | 0°   |          | 8°   | 0°    |            | 8°     |
| L    | 0.45 | 0.60     | 0.75 | 0.018 | 0.024      | 0.030  |



0087225C

Obsolete Product(s) - Obsolete Product(s)

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

© The ST logo is a registered trademark of STMicroelectronics

© 2000 STMicroelectronics - Printed in Italy - All Rights Reserved  
STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - China - Finland - France - Germany - Hong Kong - India - Italy - Japan - Malaysia - Malta - Morocco  
Singapore - Spain - Sweden - Switzerland - United Kingdom

© <http://www.st.com>