

Mass Storage : MT29F4G08AACWC

Print this page


[Overview](#)
[Resources & Support](#)
[RSS part feed:](#)


Illustration only. See data sheet for product specifications.

SPECIFICATIONS

Density: 4Gb
Part Status: Production
ROHS: Yes
Width: x8
Voltage: 3.3V
Package: TSOP
Pin Count: 48-pin
Bits/Cell: SLC
I/O: Common
Op Temp: 0C to +70C

DESCRIPTION

Micron NAND Flash uses an industry proven floating gate cell and a standard interface to enable pin and function drop-in compatibility and easy integration into most existing designs.

RoHS-Compliant: This part meets internationally recognized Pbfree standards, including RoHS.

[RoHS Certificate of Compliance](#)
[China RoHS Certificate](#)

| Orderable Part | Part Status | Buy Samples | Distributor Stock |
|------------------|-------------|-----------------------------|-----------------------|
| MT29F4G08AACWC:C | Production | Add To Cart | +View |

Please note: Distributor inventory is an estimate and may not reflect actual available inventory.

Some links on this page will take you from the Micron Web site. Micron does not control the content on these Web sites.

Resources

Documents

[4Gb, 8Gb: x8, x16 SLC NAND Flash Data Sheet \(NDA - Contact Factory\)](#)

Date: 05/08

Size: 0Kb

Type: Data Sheet (PDF)

Simulation Models

[Denali](#)

Date: 04/09

Size: 0Kb

Version: 04/09

[IBIS](#)

Date: 08/08

Size: 1494Kb

Version: (secure)

[HSpice](#)

Date: 08/08

Size: 1409Kb

Version: (secure)

[Verilog](#)

Date: 02/09

Size: 0Kb

Version: (secure)

About Micron Models :

By downloading any Micron model from this site, you must agree to the terms of [Micron's Simulation Models License Agreement](#). If you do not agree to terms, you do not have permission to use the site or download material from it.

About Non-Micron Models:

For your convenience, Micron links to third party simulation models. Note that Micron does not guarantee functionality or accuracy of these models.