To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.

Downloaded from Arrow.com.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.

   "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.

   "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.

   "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

Downloaded from Arrow.com.

To all our customers

Regarding the change of names mentioned in the document, such as Mitsubishi Electric and Mitsubishi XX, to Renesas Technology Corp.

The semiconductor operations of Hitachi and Mitsubishi Electric were transferred to Renesas Technology Corporation on April 1st 2003. These operations include microcomputer, logic, analog and discrete devices, and memory chips other than DRAMs (flash memory, SRAMs etc.) Accordingly, although Mitsubishi Electric, Mitsubishi Electric Corporation, Mitsubishi Semiconductors, and other Mitsubishi brand names are mentioned in the document, these names have in fact all been changed to Renesas Technology Corp. Thank you for your understanding. Except for our corporate trademark, logo and corporate statement, no changes whatsoever have been made to the contents of the document, and these changes do not constitute any alteration to the contents of the document itself.

Note : Mitsubishi Electric will continue the business operations of high frequency & optical devices and power devices.

Renesas Technology Corp.
Customer Support Dept.
April 1, 2003

Downloaded from Arrow.com.

M5M5W817KT - 70HI

8388608-BIT (524288-WORD BY 16-BIT / 10485776-WORD BY 8-BIT) CMOS STATIC RAM

DESCRIPTION

The M5M5W817KT is a family of low voltage 8Mbit static RAMs organized as 524288-words by 16-bit / 1048576-words by 8-bit, fabricated by Mitsubishi's high-performance 0.18µm CMOS technology.

The M5M5W817KT is suitable for memory applications where a simple interfacing, battery operating and battery backup are the important design objectives.

The M5M5W817KT is packaged in a 52pin-µTSOP with the outline of 10.79mm x 10.49mm, and pin pitch of 0.40mm. It gives the best solution for a compaction of mounting area as well as flexibility of wiring pattern of printed circuit boards.

The operating temperature range is -40 ~ +85°C


FEATURES

- Single 2.7~3.6V power supply
- Small stand-by current: 0.1µA (2.0V, typ.)
- No clocks, No refresh
- Data retention supply voltage =2.0~3.6V
- All inputs and outputs are TTL compatible.
- Easy memory expansion by S1#, S2, BC1# and BC2#
- Common Data I/O
- Three-state outputs: OR-tie capability
- OE prevents data contention in the I/O bus
- Byte function (x8 mode) available by Byte# & A-1.
- Process technology: 0.18µm CMOS
- Package: 52pin 10.79mm x 10.49mm µTSOP
  [0.4mm pin pitch]

Operating temperature	Part name	Power Supply	Access time max.	Stand-by current * Typical 25ºC	Stand-by current * Typical 40ºC	Stand-by current Ratings (max.) 25ºC	Stand-by current Ratings (max.) 40ºC	Stand-by current Ratings (max.) 70ºC	Stand-by current Ratings (max.) 85ºC	Active current Icc1 (3.3V, Typ.)
-40 ~ +85°C	M5M5W817KT -70HI	2.7 ~ 3.6V	70ns	1.0	1.2	5	8	20	40	30mA (10MHz) 5mA (1MHz)

PIN CONFIGURATION

* Typical parameter indicates the value for the center of distribution, and not 100% tested.



Pin	Function
A0 ~ A18	Address input
DQ1 ~ DQ16	Data input / output
S1#	Chip select input 1
S2	Chip select input 2
W#	Write control input
OE#	Output enable input
BC1#	Lower Byte (DQ1 ~ 8)
BC2#	Upper Byte (DQ9 ~ 16)
BYTE#	Byte (x8 mode) enable input
Vcc	Power supply
GND	Ground supply

Outline: 52PTG-A
N C : No Connection

Downloaded from Arrow.com.

M5M5W817KT - 70HI

8388608-BIT (524288-WORD BY 16-BIT / 10485776-WORD BY 8-BIT) CMOS STATIC RAM

FUNCTION

The M5M5W817KT is organized as 524288-words by 16-bit / 1048576-words by 8-bit. These devices operate on a single +2.7~3.6V power supply, and are directly TTL compatible to both input and output. Its fully static circuit needs no clocks and no refresh, and makes it useful.

The operation mode are determined by a combination of the device control inputs BC1# , BC2# , S1#, S2 , W#, OE# and BYTE#. Each mode is summarized in the function table.

A write operation is executed whenever the low level W# overlaps with the low level BC1# and/or BC2# and the low level S1# and the high level S2. The address (A-1~A18 : Byte mode, A0~A18 : Word mode) must be set up before the write cycle and must be stable during the entire cycle.

A read operation is executed by setting W# at a high level and OE# at a low level while BC1# and/or BC2# and S1#and S2 are in an active state (S1#=L, S2=H).

When setting BYTE# at a low level, the function will be in the x8 mede, which is, DQ1-8 are available and DQ9-16 are not available. In the x8 mode, A-1 is used as the additional address. During the active function for x8 mode, BC1# BC2# must be low level.

When setting BC1# and BC2# at a high level or S1# at a high level or S2 at a low level, the chips are in a non-selectable mode in which both reading and writing are disabled.

In this mode, the output stage is in a high-impedance state, allowing OR-tie with other chips and memory expansion by BC1#, BC2# and S1#, S2.

The power supply current is reduced as low as 0.1µA (25°C, typical), and the memory data can be held at +2.0V power supply, enabling battery back-up operation during power failure or power-down operation in the non-selected mode.


FUNCTION TABLE

S1#	S2	BYTE#	BC1#	BC2#	W#	OE#	Mode	DQ1~8	DQ9~15	DQ16	Icc
H	H	H or L	X	X	X	X	Non selection	High-Z	High-Z	High-Z	Standby
X	L	H or L	X	X	X	X	Non selection	High-Z	High-Z	High-Z	Standby
X	X	H	H	H	X	X	Non selection	High-Z	High-Z	High-Z	Standby
L	H	H	L	H	L	X	Write	Din	High-Z	High-Z	Active
L	H	H	L	H	H	L	Read	Dout	High-Z	High-Z	Active
L	H	H	L	H	H	H	-------	High-Z	High-Z	High-Z	Active
L	H	H	H	L	L	X	Write	High-Z	Din	Din	Active
L	H	H	H	L	H	L	Read	High-Z	Dout	Dout	Active
L	H	H	H	L	H	X	-------	High-Z	High-Z	High-Z	Active
L	H	H	L	L	L	X	Write	Din	Din	Din	Active
L	H	H	L	L	H	L	Read	Dout	Dout	Dout	Active
L	H	H	L	L	H	X	-------	High-Z	High-Z	High-Z	Active
L	H	L	L	L	L	X	Write	Din	High-Z	A-1	Active
L	H	L	L	L	H	L	Read	Dout	High-Z	A-1	Active
L	H	L	L	L	H	H	-------	High-Z	High-Z	A-1	Active

Note1 : "H" and "L" in this table mean V_{IH} and V_{IL}, respectively.
Note2 : "X" in this table should be "H" or "L".

Downloaded from Arrow.com.

BLOCK DIAGRAM



Downloaded from Arrow.com.

ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Conditions	Ratings	Units
V_{CC}	Supply voltage	With respect to GND	- 0.3* ~ +4.6	V
V_I	Input voltage	With respect to GND	- 0.3* ~ Vcc + 0.3 (max. 4.6V)	
V_O	Output voltage	With respect to GND	0 ~ Vcc	
P_d	Power dissipation	Ta = 25°C	700	mW
T_a	Operating temperature		-40 ~ +85	°C
T_{stg}	Storage temperature		- 65 ~ +150	°C

* -3.0V in case of AC (Pulse width ≦ 30ns)

DC ELECTRICAL CHARACTERISTICS (Ta=-40~85°C Vcc=2.7V~3.6V,unless otherwise noted)

Symbol	Parameter	Conditions		Limits Min	Limits Typ	Limits Max	Units
V_{IH}	High-level input voltage			2.2		Vcc+0.2V	V
V_{IL}	Low-level input voltage			- 0.2 *		0.6	
V_{OH}	High-level output voltage	I_{OH}= - 0.5mA		2.4			
V_{OL}	Low-level output voltage	I_{OL}= 2.0mA				0.4	
I_I	Input leakage current	V_I =0 ~ Vcc				±1	µA
I_O	Output leakage current	BC1# and BC2#=VIH or S1#=VIH or S2=VIL or OE#=VIH, VI/O=0 ~ Vcc				±1	
Icc1	Active supply current (AC,MOS level)	BC1# and BC2# ≦ 0.2V, S1# ≦ 0.2V, S2 ≧Vcc-0.2V other inputs ≦ 0.2V or ≧ Vcc-0.2V Output - open (duty 100%)	f= 10MHz	-	30	50	mA
			f= 1MHz	-	5	15	
Icc2	Active supply current (AC,TTL level)	BC1# and BC2#=VIL , S1#=VIL ,S2=VIH other pins =VIH or VIL Output - open (duty 100%)	f= 10MHz	-	30	50	
			f= 1MHz	-	5	15	
Icc3	Stand by supply current (AC,MOS level)	(1) S1# ≧ Vcc - 0.2V and S2 ≧ Vcc - 0.2V, BYTE# ≧ Vcc - 0.2V or ≦ 0.2V, other inputs = 0 ~ Vcc	~ +25°C	-	1.0	5	µA
		(2) S2 ≦ 0.2V, BYTE# ≧ Vcc - 0.2V or ≦ 0.2V, other inputs = 0 ~ Vcc	~ +40°C	-	1.2	8	
		(3) BC1# and BC2# ≧ Vcc - 0.2V S1# ≦ 0.2V, S2 ≧ Vcc - 0.2V BYTE# ≧ Vcc - 0.2V or ≦ 0.2V, other inputs = 0 ~ Vcc	~ +70°C	-	-	20	
			~ +85°C	-	-	40	
Icc4	Stand by supply current (AC,TTL level)	BC1# and BC2# =VIH or S1# =VIH or S2=VIL BYTE# ≧ Vcc - 0.2V or ≦ 0.2V, Other inputs= 0 ~ Vcc		-	-	2.0	mA

* -1.0V in case of AC (Pulse width ≦ 30ns)

Note 3: Direction for current flowing into IC is indicated as positive (no mark)
Note 4: Typical parameter indicates the value for the center of distribution at 3.0V, and not 100% tested.

CAPACITANCE (Ta=-40~+85°C Vcc=2.7V~3.6V,unless otherwise noted)

Symbol	Parameter	Conditions	Limits Min	Limits Typ	Limits Max	Units
C_I	Input capacitance	V_I=GND, V_I=25mVrms, f=1MHz			10	pF
C_O	Output capacitance	V_O=GND, V_O=25mVrms, f=1MHz			10	

Downloaded from Arrow.com.

AC ELECTRICAL CHARACTERISTICS (Ta=-40~+85ºC, Vcc=2.7V~3.6V,unless otherwise noted)

(1) TEST CONDITIONS

Supply voltage	2.7~3.6V
Input pulse	V_{IH}=2.7V, V_{IL}=0.2V
Input rise time and fall time	5ns
Reference level	V_{OH}=V_{OL}=1.5V Transition is measured ±200mV from steady state voltage.(for ten,tdis)
Output loads	Fig.1,CL=30pF CL=5pF (for ten,tdis)




Fig.1 Output load

(2) READ CYCLE

Symbol	Parameter	Limits 70HI Min	Limits 70HI Max	Units
t_{CR}	Read cycle time	70		ns
t_a(A)	Address access time		70	ns
t_a(S1)	Chip select 1 access time		70	ns
t_a(S2)	Chip select 2 access time		70	ns
t_a(BC1)	Byte control 1 access time		70	ns
t_a(BC2)	Byte control 2 access time		70	ns
t_a(OE)	Output enable access time		35	ns
t_{dis}(S1)	Output disable time after S1# high		25	ns
t_{dis}(S2)	Output disable time after S2 low		25	ns
t_{dis}(BC1)	Output disable time after BC1# high		25	ns
t_{dis}(BC2)	Output disable time after BC2# high		25	ns
t_{dis}(OE)	Output disable time after OE# high		25	ns
t_{en}(S1)	Output enable time after S1# low	10		ns
t_{en}(S2)	Output enable time after S2 high	10		ns
t_{en}(BC1)	Output enable time after BC1# low	5		ns
t_{en}(BC2)	Output enable time after BC2# low	5		ns
t_{en}(OE)	Output enable time after OE# low	5		ns
t_V(A)	Data valid time after address	10		ns

(3) WRITE CYCLE

Symbol	Parameter	Limits 70HI Min	Limits 70HI Max	Units
t_{CW}	Write cycle time	70		ns
t_w(W)	Write pulse width	55		ns
t_{su}(A)	Address setup time	0		ns
t_{su}(A-WH)	Address setup time with respect to W#	65		ns
t_{su}(BC1)	Byte control 1 setup time	65		ns
t_{su}(BC2)	Byte control 2 setup time	65		ns
t_{su}(S1)	Chip select 1 setup time	65		ns
t_{su}(S2)	Chip select 2 setup time	65		ns
t_{su}(D)	Data setup time	35		ns
t_h(D)	Data hold time	0		ns
t_{rec}(W)	Write recovery time	0		ns
t_{dis}(W)	Output disable time from W# low		25	ns
t_{dis}(OE)	Output disable time from OE# high		25	ns
t_{en}(W)	Output enable time from W# high	5		ns
t_{en}(OE)	Output enable time from OE# low	5		ns


Downloaded from Arrow.com.

(4) Byte# function


Symbol	Parameter	Test conditions	Limits			Units
			Min	Typ	Max	
$t_{su\ (BYTE)}$	BYTE# set up time		5			ms
$t_{rec\ (BYTE)}$	BYTE# recovery time		5			ms

(5) TIMING DIAGRAMS

BYTE#




Read cycle




Downloaded from Arrow.com.

Write cycle(W# control mode)



Write cycle (BC# control mode)



Note 5: Hatching indicates the state is "don't care".


Note 6: A Write occurs during S1# low, S2 high overlaps BC1# and/or BC2# low and W# low.

Note 7: When the falling edge of W# is simultaneously or prior to the falling edge of BC1# and/or BC2# or the falling edge of S1# or rising edge of S2, the outputs are maintained in the high impedance state.


Note 8: Don't apply inverted phase signal externally when DQ pin is in output mode.

Downloaded from Arrow.com.

Write cycle (S1# control mode)



Write cycle (S2 control mode)



Downloaded from Arrow.com.

POWER DOWN CHARACTERISTICS

(1) ELECTRICAL CHARACTERISTICS (Ta=-40~85ºC, Vcc=2.7V~3.6V,unless otherwise noted)

Symbol	Parameter	Test conditions		Limits Min	Limits Typ	Limits Max	Units
Vcc (PD)	Power down supply voltage			2.0			V
VI (BC)	Byte control input BC1# & BC2#			2.0			V
VI (S1#)	Chip select input S1#			2.0			V
VI (S2)	Chip select input S2					0.2	V
Icc (PD)	Power down supply current	**Vcc=2.0V** (1) S1# ≥ Vcc - 0.2V, BYTE# ≥ Vcc - 0.2V or ≤ 0.2V other inputs = 0 ~ Vcc (2) S2 ≤ 0.2V , BYTE# ≥ Vcc - 0.2V or ≤ 0.2V other inputs = 0 ~ Vcc (3) BC1# and BC2# ≥ Vcc - 0.2V S1# ≤ 0.2V, S2 ≥ Vcc - 0.2V BYTE# ≥ Vcc - 0.2V or ≤ 0.2V other inputs = 0 ~ Vcc	~ +25°C	-	0.2	3.0	µA
			~ +40°C	-	0.4	6.0	
			~ +70°C	-	-	30	
			~ +85°C	-	-	60	

Note 9: Typical parameter of Icc(PD) indicates the value for the center of distribution at 2.0V, and not 100% tested.


(2) TIMING REQUIREMENTS

Symbol	Parameter	Test conditions	Limits Min	Limits Typ	Limits Max	Units
tsu (PD)	Power down set up time		0			ns
trec (PD)	Power down recovery time		5			ms

(3) TIMING DIAGRAM


BC# control mode

note10:On the BC# control mode, the level of S1# and S2 must be fixed at S1#, S2 ≥ Vcc-0.2V or S2 ≤0.2V




S1# control mode

note11:On the S1# control mode, the level of S2 must be fixed at S2 ≥ Vcc-0.2V or S2 ≤0.2V



S2 control mode



Downloaded from Arrow.com.

M5M5W817KT - 70HI

8388608-BIT (524288-WORD BY 16-BIT / 10485776-WORD BY 8-BIT) CMOS STATIC RAM

Keep safety first in your circuit designs!

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products betterand more reliable, but there isalways the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

These materials are intended as a reference to assist our customers in the selection of the Mitsubishi semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.

Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.

All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Semiconductor product distributor for the latest product information before purchasing a product listed herein.

The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Semiconductor home page (http://www.mitsubishichips.com).

When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.

Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.

The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.

If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination. Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.

Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Semiconductor product distributor for further details on these materials or the products contained therein.

Downloaded from Arrow.com.