







P/N: SEE TABLE
S/N: Y = YEAR, THE LAST DIGIT OF YEAR
DDD = DAY OF THE YEAR
L = LOCATION
1 - USA
2 - MEXICO
3 - CHINA

SSSS = SERIAL NUMBER
X.XXM: CABLE LENGTH, SEE TABLE
XXAWG: WIRE GAGE, SEE TABLE

(DATE CODE ISO-8601 FORMAT)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#517487				molex MINISAS 4X HD TO MINISAS 4X HD 12GB EXT PASSIVE CBL ASSY							
MM		1:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)															
ANGULAR TOL		± °													
4 PLACES		±													
3 PLACES		±													
2 PLACES		± 0.130		STATUS: Production DRWN: J Sanat Kumar 2025-11-24 CHK'D: Ganesh Rao B 2026-01-23 APPR: Gurunandan GA 2026-01-23				PRODUCT CUSTOMER DRAWING							
1 PLACE		± 0.25						DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
0 PLACES		±						1110751000		PSD		000		J1	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						D-SIZE		111075		SEE PN TABLE		GENERAL MARKET		3 OF 3	




MOLEX P/N	LENGTH (M)	LENGTH TOLERANCE (MM)	AWG
1110751000	0.5	±25	30
1110751001	1.0	±50	30
1110751160	1.45	±50	30
1110753112	1.5	±50	30
1110751002	2.0	±50	30
1110751025	2.5	±50	28
1110751003	3.0	±100	28
1110751026	3.5	±100	28
1110751004	4.0	±100	26
1110751005	5.0	±100	26
1110751027	5.5	±100	26
1110751006	6.0	±100	26
1110751008	8.0	±150	24

NOTES :

1. MATERIAL =
BACKSHELLS - NICKEL PLATED ZINC DIECAST.
LATCH - STAINLESS STEEL.
PULL - HALOGEN FREE THERMOPLASTIC ELASTOMER (TPE)
2. THIS PRODUCT CONFORMS TO THE MECHANICAL DIMENSIONING OF SFF-8644 AND ELECTRICAL PERFORMANCE REQUIREMENTS OF SAS 3.0
3. RoHS COMPLIANT. NO EXEMPTIONS.
4. TAPE CABLE BUNDLES EVERY 1/2 METER (APPROXIMATELY)
5. PROTECTIVE DUST CAP TO BE INSTALLED ONTO EACH PLUG (NOT SHOWN).

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																								
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#517487				molex MINISAS 4X HD TO MINISAS 4X HD 12GB EXT PASSIVE CBL ASSY																
MM		2:1																						
GENERAL TOLERANCES (UNLESS SPECIFIED)																								
4 PLACES		±		±		STATUS: Production DRWN: J Sanat Kumar 2025-12-03 CHK'D: Ganesh Rao B 2026-01-23 APPR: Gurunandan GA 2026-01-23 INITIAL REVISION: DRWN: RKLIN 2012-09-11 APPR: RMKHAN 2013-07-03																		
3 PLACES		±		±																				
2 PLACES		± 0.130		±																				
1 PLACE		± 0.25		±																				
0 PLACES		±		±																				
ANGULAR TOL		± *		PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-111075-1000 DOC TYPE PSD DOC PART 001 REVISION H																				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
																	D-SIZE		111075		SEE P/N TABLE		GENERAL MARKET	



P/N: SEE TABLE
S/N: Y = YEAR, LAST DIGIT OF YEAR
DDD = DAY OF THE YEAR
L = LOCATION - 1 = USA
2 = MEXICO
3 = CHINA
SSSS = SERIAL NUMBER
X.XXM: CABLE LENGTH, SEE TABLE
XXAWG: WIRE GAGE, SEE TABLE

(DATE CODE ISO-8601 FORMAT)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#517487				molex MINISAS 4X HD TO MINISAS 4X HD 12GB EXT PASSIVE CBL ASSY				
MM		3:1										
GENERAL TOLERANCES (UNLESS SPECIFIED)												
		MM	INCH									
4 PLACES	±		±	STATUS: Production DRWN: J Sanat Kumar 2025-12-03 CHK'D: Ganesh Rao B 2026-01-23 APPR: Gurunandan GA 2026-01-23				PRODUCT CUSTOMER DRAWING				
3 PLACES	±		±									
2 PLACES	±	0.130	±									
1 PLACE	±	0.25	±	INITIAL REVISION: DRWN: RKLIN 2012-09-11 APPR: RMKHAN 2013-07-03				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
0 PLACES	±		±					SD-111075-1000		PSD	001	H
ANGULAR TOL		±	°									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
						D-SIZE	111075	SEE P/N TABLE		GENERAL MARKET		3 OF 3