



Home> Products > MICRO SWITCH™ Global Limit Switches> GLL > Product Page

GLLA06B



Actual product appearance may vary.

Global Limit Switches Series GLL: Top Plunger, 2NC Direct Opening Slow Action, 1/2 in conduit

Features

- Double break, directopening snap action contacts conform to IEC 609475-1-3
- c-UL-US, CE, CCC approvals
- Snap action and slow action circuitry
- EN50047 mounting
- 20 mm and 1/2 in NPT conduit openings
- Galvanically isolated contacts
- Double insulated plastic housing
- Contact block integral to switch housing
- Hinge cover for easy wiring access
- Sealing IP65; NEMA 1, 12, and 13

Potential Applications

- Elevators
- Escalators
- Aerial/platform lifts
- Industrial doors
- Packaging equipment

Description

Honeywell's GLL limit switch is part of the OEM set of miniature limit switches. It combines and enhances the existing GLS, SZL-VL, and EVN switches into one common family, competitively priced for OEM applications. The double insulated compact housing conforms to EN50047 and makes GLL switches often ideal for mounting where space is at a premium. These products feature direct opening, normally closed contacts The GLL Series is available in a variety of actuator styles required for OEM applications. Designed to the IEC electrical standard, the GLL is suitable for worldwide use and also meets globally accepted mounting standards.

Supporting Documentation

-  [Installation Instructions](#)
-  [Instructions for reading bar charts](#)

Product Specifications	
Availability	Global
Operating Force (O.F.)	6,0 N [1.35 lb]
Pretravel (P.T.)	2,0 mm max. [0.08 in]
Overtravel (O.T.)	3,0 mm min. [0.12 in min.]
Differential Travel (D.T.)	NA
Product Type	EN 50047 Global Limit Switch
Actuator	Top Plunger
Lever Style	None
Circuitry	2NC Slow Action
Ampere Rating	10 A (Thermal)
Supply Voltage	300 Vac and 250 Vdc max.
Housing Material	Plastic
Termination Type	12,7 mm [0.5 in] conduit
Housing Type	EN 50047
Series Name	GLL
Shock	50 g per IEC 68 - 2 - 27c (w/o Actuator)
Vibration	10 g per IEC 68 - 2 - 6 (w/o Actuator)
Sealing	IP65, NEMA 1, 12, 13
Approvals	c- UL - us, CE, CCC
CSA File #	E216958
UL File #	E216958
Mechanical Life	5 million operations
Operating Temperature Range	- 10 °C to 80 °C [14 °F to 176 °F]
Comment	Top plunger; 12,7 mm [0.5 in] conduit
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial
Operating Position (O.P.)	19,5 mm; 0.5 mm [0.77 in; 0.02 in]

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control▼

Product Search

Part number search:

Use (*) to expand search

Specification Search