



**Part Number :** [2047110011](#)

**Product Description :** Universal Serial Bus (USB)  
Shielded I/O Receptacle, Type C, Vertical, Surface  
Mount, Spring Shell, 1.40mm Tab, Gold (Au) Plating

**Series Number :** 204711

**Status :** Active

**Product Category :** I/O Connectors



---

## Documents and Resources

### Drawings

[2047110011\\_sd.pdf](#)

[2047118888-000.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications


[PS-105448-001-001.pdf](#)

[2047110001-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	I/O Connectors
Series	204711
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Vertical, Surface Mount, Spring Shell, 1.40mm Tab, Gold (Au) Plating
Application	Wire-to-Board
Component Type	Receptacle
IEC Compliance	62680-1-3:2022, 62680-1-2:2022
Product Name	USB
Standard	USB 3.2 Gen 2
Type	C
UPC	198282801139
USB-IF/TID	12613

### Electrical

Current - Maximum per Contact	0.25A,1.25A,5.0A, See Product Specification
Grounding to Panel	None
Shielded	Yes

Shield Type	Full Shield
Voltage - Maximum	30V AC/DC

## Physical

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Mounting Style	Vertical
Net Weight	0.686/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	0.70mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.760µm
Plating min - Termination	0.051µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-30° to +85°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
USB Shielded I/O Type C Plugs	<u>105444</u>

---

This document was generated on May 15, 2026