





REV. B
DCO 300781

TOLERANCES ±.010" - UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C

RESISTANCE	320 OHMS ±10%
NOMINAL VOLTAGE	28 VDC
MUST OPERATE	13.5 VDC MAX.
	TRANSIENT SUPPRESSION - 42 VDC MAX.
MUST RELEASE	5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:


VIBRATION 10 Hz TO 3000 Hz @ 30 g's

SHOCK 200 g's 6 MS. DURATION

TEMPERATURE -70 °C TO +125 °C

NOTES:
1. OPERATE, RELEASE 10 MS MAX.
2. CONTACT STABILIZATION 2.5 MS MAX.
3. CONTACT BOUNCE 1 MS MAX.
4. CONTACT BREAK BOUNCE 0.1 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL
TO 10 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE,
100,000 OPERATIONS

DR. B.D. 05MAR2008 | CK. 3/7/08 J.M.B.

Tyco Electronics
©COPYRIGHT 2005
TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CUST.

CUST. NO. M83536/10-026M REV. ---

TE NUMBER
2-1617749-4

CII PART NUMBER
FCA-210-1026M

Downloaded from Arrow.com.