



Type label identification, thermal transfer


Helatag 1204 (Silver)

Scratch-resistant type plates for the industry. The high temperature range suits a wide range of applications on flat surfaces. The adhesive is also suitable for critical surfaces like plastic and paint.

Designing and printing labels is simple and users can quickly print out professional labels in a matter of moments when using TagPrint Pro labelling software.

Features and Benefits

- Marking labels made of matt silver Polyester
- Replacement option for aluminium plates
- Print labels with customer unique references
- Use text, graphics and barcodes as required
- Excellent print performance using TT822OUT ribbon
- Print with TT4000+, TT430 for best results
- Easy label design with Tagprint Pro



Professional type plate on a heating unit.

MATERIAL	Type 1204, Polyester (PET), silver matt (SR)
Operating Temperature	-40 °C to +150 °C
Curing Temperature	from 0 °C
Adhesive	Acrylic
Thickness of Foil (µm)	55 µm
Chem. Material Properties	Excellent resistance to water, alcohol, most oils, greases, fuel, aliphatic solvents, weak acids, salts and alkalis.
Recommended Ribbon Type	TT822OUT
Specifications	UL-Recognised



TYPE	Width (W)	Height (H)	Width of Liner (WL)	Labels per Row	Pack Cont.	Colour	Article-No.
TAG71TD6-1204-SR	12.7	11.1	101.6	6	15,000 pcs.	Silver (SR)	596-12071
TAG13TD4-1204-SR	19.1	6.4	101.6	4	10,000 pcs.	Silver (SR)	596-12043
TAG34TD3-1204-SR	25.4	9.5	85.1	3	7,500 pcs.	Silver (SR)	596-34120
TAG15TD3-1204-SR	25.4	12.7	85.1	3	7,500 pcs.	Silver (SR)	596-12045
TAG35TD3-1204-SR	31.8	9.5	101.6	3	7,500 pcs.	Silver (SR)	596-12035
TAG17TD2-1204-SR	38.1	6.4	85.1	2	5,000 pcs.	Silver (SR)	596-12047
TAG27TD2-1204-SR	38.1	19.1	85.1	2	5,000 pcs.	Silver (SR)	596-27120
TAG67TD2-1204-SR	38.1	31.8	85.1	2	1,000 pcs.	Silver (SR)	596-12067
TAG69TD2-1204-SR	40.6	22.9	89.0	2	2,500 pcs.	Silver (SR)	596-12069
TAG77TD1-1204-SR	50.8	22.9	55.0	1	2,000 pcs.	Silver (SR)	596-12077
TAG73TD1-1204-SR	50.8	25.4	55.0	1	2,000 pcs.	Silver (SR)	596-73124
TAG66TD1-1204-SR	50.8	36.5	56.8	1	1,000 pcs.	Silver (SR)	596-12066
TAG63TD1-1204-SR	63.5	38.1	70.0	1	1,000 pcs.	Silver (SR)	596-12063
TAG76TD1-1204-SR	63.5	50.8	70.0	1	500 pcs.	Silver (SR)	596-12076
TAG72TD1-1204-SR	69.9	31.8	76.0	1	1,000 pcs.	Silver (SR)	596-12072

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.




For product specific approvals and specifications please refer to the Appendix.



Type label identification, thermal transfer

Helatag 1204 (Silver)



TYPE	Width (W)	Height (H)	Width of Liner (WL)	Labels per Row	Pack Cont.	Colour	Article-No.
TAG65TD1-1204-SR	76.2	36.5	82.0	1	1,000 pcs.	Silver (SR)	596-12065
TAG62TD1-1204-SR	76.2	50.8	82.0	1	500 pcs.	Silver (SR)	596-12062
TAG64TD1-1204-SR	88.9	36.5	95.0	1	1,000 pcs.	Silver (SR)	596-12064
TAG97TD1-1204-SR	101.6	74.0	106.0	1	500 pcs.	Silver (SR)	596-71204
TAGR3TD1-1204-SR	104.0	-	108.0	1	75.0 m	Silver (SR)	596-31204
TAG02TD1-1204-SR	104.0	12.0	104.0	1	5,000 pcs.	Silver (SR)	596-21204

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.

Asset identification label, thermal transfer

Helatag 1206 (White)

Scratch-resistant general identification for industrial applications. The high temperature range suits a wide range of applications on flat surfaces. The adhesive is also suitable for critical surfaces such as plastic and paint coated.

Features and Benefits

- Ideal for machinery operating in high temperature areas (up to +150 °C)
- Barcodes and alphanumeric text remain pin sharp on this high quality material
- Excellent print performance using TT822OUT ribbon
- Print with TT4000+, TT430 for best results
- Easy label design with Tagprint Pro



Helatag label for a permanent asset identification.

MATERIAL	Type 1206, Polyester (PET), white gloss (GSWH)
Operating Temperature	-40 °C to +150 °C
Curing Temperature	from 0 °C
Adhesive	Acrylic
Thickness of Foil (µm)	50 µm
Chem. Material Properties	Excellent resistance to water, alcohol, most oils, greases, fuel, aliphatic solvents, weak acids, salts and alkalis.
Recommended Ribbon Type	TT822OUT
Specifications	UL-Recognised

