

Johanson Part Number Information

11-13-2022

Johanson Part Number:	LRC0402CS4N7GV001T	Johanson Company:	Johanson Technology Inc.
Legacy P/N:	L-07C4N7SV6T	NCNR:	No
Description:	Ceramic Inductor, 0402, 4.7nH±0.3nH, 300mA, Ni/Sn (RoHS), Orientation Mark Full Marking, 7" Reel Paper Tape	Thickness (Max):	0.024
		Thickness (Min):	0.016
Life Cycle Stage:	Active - Production	End Band (Max):	0.013
AEC Q200 Qualified:	No	Standard Item:	No
Schedule B:	8504.50.0000	Lead Time Typical (Weeks)*:	
Harmonization Code:	8504.50.40.00	*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.	14
ITAR:	No	Length (Min):	0.035
ECCN:	EAR99	Length (Max):	0.043
RoHS Compliance:	Yes, RoHS 10/10	Width (Min):	0.016
REACH:	Yes	Width (Max):	0.024
Country of Origin:	TW	Part Weight (mg):	0.980
Product Family:	Inductors	Packaged Weight (lb) Arm:	0.300
Product Subfamily:	Ceramic Inductors	Packaging:	7" Reel Paper Tape
Tolerance:	±0.3nH	Packaging Qty:	10000
Termination:	Ni/Sn (RoHS)	Operating Temp Range:	-40°C to + 100°C
Marking:	Orientation Mark Full Marking	Storage Temp Range (Packaged):	-10°C to +40°C
Product Release Date:	03 January, 2006	Storage Temp Range (Non Operating):	-40°C to +125°C
Web Page Link:		Download this information page	

QUICK LINKS

- ▶ Home
- ▶ About
- ▶ Contact Us
- ▶ News
- ▶ Do Not Sell My Personal Information

CERTIFICATIONS



VISIT OUR SISTER SITE:



Johanson Technology is dedicated to providing the highest level of customer satisfaction through high quality components, superior customer service and forward looking, advanced products.