



**Part Number :** [524652470](#)

**Product Description :** SlimStack Board-to-Board Connector, 0.80mm Pitch, Rigid Type Receptacle, 4.50 or 5.65mm Mated Height, Vertical, 24 Circuits, with Boss

**Series Number :** 52465

**Status :** Active

**Product Category :** Board-to-Board Connectors



---

## Documents and Resources

### Drawings

[524652470 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[SPK-52465-002-001.pdf](#)

[PS-52465-010-001.pdf](#)


[PS-52465-014-001.pdf](#)

[PS-52465-015-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS

Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	Board-to-Board Connectors
Series	0.8 and above
Description	SlimStack Board-to-Board Connector, 0.80mm Pitch, Rigid Type Receptacle, 4.50 or 5.65mm Mated Height, Vertical, 24 Circuits, with Boss
Application	Board-to-Board, Signal
Component Type	Receptacle
Product Name	SlimStack
UPC	822348203789

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

**Physical**

Circuits (Loaded)	24
-------------------	----

Circuits (maximum)	24
Color - Resin	Natural
Durability (mating cycles max)	30
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Mated Height	4.50mm, 5.65mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	259.189/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	0.80mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
0.80mm Pitch Vertical SlimStack Plugs	<a href="#"><u>53307</u></a>
0.80mm Pitch Right-Angle SlimStack Plugs	<a href="#"><u>53309</u></a>

---

This document was generated on Jun 04, 2026