

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RW82444-A2

BZ-2RW82444-A2

M

DRAWING
NUMBER

4

ISSUE

REPLACES X82454-BZ

RELEASE NO. PR-14435

CHECK

REVISIONS

A	CO-73287-J	JAL	22 NOV 93
B	CO-7758H	KDR	29 MAR 94
C	C093346	DLT	28 AUG 98

CHECK


7 JAN 90

85 CHECK KAG

T S K 30 DEC

FORMTEK

FO-52848-A




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - SWITCH WILL WITHSTAND TEMPERATURE OF 400°F
- 3 - SWITCH CHARACTERISTICS MAY SHIFT AFTER PROLONGED EXPOSURE TO 400°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - 2 1/2 OZ MAX
RELEASE FORCE - - - - - 1/2 OZ MIN
DIFFERENTIAL TRAVEL - - - .007 - .050
OVERTRAVEL - - - - - .219 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L35 5A 125, 250, OR 480 VAC
1/2 A 125 VDC, 1/4 A 250 VDC

L288



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 2

	DIM. in	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	17/64	X	0.01/60
ONE PLACE	X.X	0.4/818	X.X	0.01/60
TWO PLACES	X.XX	0.16/406	X.XX	0.007/618
THREE PLACES	X.XXX		X.XXX	0.13/308

DESIGN UNITS ☐ SI METRIC ☐ US CUSTOMARY

WEIGHT .073 LB