

LEAD FREE PART NUMBER



SHELL	A±0.38	B±0.12	C±0.10	D +0.25 0	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15 0	D09P81C4PL00LF	D09P81C6PL00LF
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15 0	D15P81C4PL00LF	D15P81C6PL00LF
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25 0	D25P81C4PL00LF	D25P81C6PL00LF
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25 0	D37P81C4PL00LF	D37P81C6PL00LF
Gold flash							0.76 μ gold	

Detail of grounding strip

PC card drilling dimensions(after plating)
(thickness 1.60 ±0.20)

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ✓	ISO 406 ISO 1101	 MM scale 2:1	D-SUB		
ltr	ecn no	dr	date	tolerances unless	otherwise specified		title		
G	ELX-I-18050	MP	2014/06/23	angles	.0±0.1		MALE CONNECTOR DELTA-D EUROPE		
H	ELX-I-34612	GM	2019-20-08	linear	.00±0.1		RIGHT ANGLED PRESS FIT		
				0°±2°	.000±0.1		dwg no		
				dr	JOUBERT	1996/12/06	sheet 1 of 1		
				enr	GREGAR M	2014/06/23	size		
				chr	MITHUN PAUL	2019-20-08	C01-8646-0583		
				appd	SANOJ P K	2019-20-08	A3		
sheet index		revision sheet	H				type Product Customer Drawing		
		1							