

Low ESR, 2.7V Radial Supercapacitor

F 10F 10F 10F
V 2.7V 2.7V 2.7V

ADCR-E02R7S

Request Samples



Check Inventory



Various Sizes

RoHS/RoHS II Compliant

MSL Level = 1

Features

- Very Low internal resistance (ESR)
- High power density
- Minimal discharge rate, 72 hours @ discharge<20%
- Excellent cycle life
- Green, meet RoHS requirements

Applications

- Power Assist Circuits
- Power Backup
- Micro Energy Storage
- IoT Energy Harvesting
- SSD applications
- DDR power back up
- RTC System power transfer to battery backup

Electrical Specifications

Part Number	Nominal Voltage (U _R)	Capacitance	Tol.	ESR (Max)	Nominal Current	Peak Current (Max)	Leakage Current	Stored Energy (Max)	Gravimetric Energy Density	Power Density	Volumetric Energy Density
ADCR-E02R7S	DC(V)	Farads	±%	mΩ	A	A	mA	mWh	Wh/kg	kW/kg	Wh/L
ADCR-E02R7SA504MB	2.7V	0.5	20	280	0.13	0.59	0.013	0.51	0.72	4.65	1.31
ADCR-E02R7SA105MB	2.7V	1	20	240	0.26	1.09	0.016	1.01	1.58	5.93	2.59
ADCR-E02R7SB105MB	2.7V	1	20	200	0.26	1.13	0.016	1.01	0.99	4.47	1.55
ADCR-E02R7SA205MB	2.7V	2	20	140	0.51	2.11	0.018	2.03	0.96	3.10	2.02
ADCR-E02R7SA335MB	2.7V	3.3	20	80	0.85	3.52	0.021	3.34	1.57	5.35	3.32
ADCR-E02R7SA505MB	2.7V	5	20	60	1.27	5.19	0.030	5.06	1.43	4.29	4.19
ADCR-E02R7SB505MB	2.7V	5	20	60	1.27	5.19	0.030	5.06	1.00	3.00	3.22
ADCR-E02R7SA605MB	2.7V	6	20	55	1.52	6.09	0.036	6.08	1.20	3.27	3.87
ADCR-E02R7SA705MB	2.7V	7	20	50	1.77	7.00	0.042	7.09	1.14	2.93	4.51
ADCR-E02R7SA106MB	2.7V	10	20	45	2.48	9.31	0.050	10.13	1.00	2.00	5.16

Operating Temperature: -40°C to +70°C

Storage Temperature: -30°C to +50°C, RH<60%, Max. Humidity <85% RH

Test Conditions: +25°C

All parameters are measured according to the IEC 62391-1 standard.

Capacitance and ESR are measured with $I(\text{mA}) = 8(C \cdot U_R)$

Nominal Current: 5 Seconds to discharge from U_R to $1/2 U_R$

Peak Current (Max.): 1 second to discharge to U_R to $1/2 U_R$

Leakage Current: Measured after 72h at U_R



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION: C 12/2/2024

ABRACON IS
ISO9001-2015
CERTIFIED

Low ESR, 2.7V Radial Supercapacitor



ADCR-E02R7S

Request Samples



Check Inventory




Various Sizes

RoHS/RoHS II Compliant

MSL Level = 1

Mechanical Specifications



Dimensions	D	L	P	d
ADCR-E02R7SA504MB	6.3±1.0	12.5±1.5	2.5±0.5	0.5±0.05
ADCR-E02R7SA105MB	6.3±1.0	12.5±1.5	2.5±0.5	0.5±0.05
ADCR-E02R7SB105MB	8±1.0	13±1.5	3.5±0.5	0.6±0.05
ADCR-E02R7SA205MB	8±1.0	20±1.5	3.5±0.5	0.6±0.05
ADCR-E02R7SA335MB	8±1.0	20±1.5	3.5±0.5	0.6±0.05
ADCR-E02R7SA505MB	8±1.0	24±1.5	3.5±0.5	0.6±0.05
ADCR-E02R7SB505MB	10±1.0	20±1.5	5.0±0.5	0.6±0.05
ADCR-E02R7SA605MB	10±1.0	20±1.5	5.0±0.5	0.6±0.05
ADCR-E02R7SA705MB	10±1.0	20±1.5	5.0±0.5	0.6±0.05
ADCR-E02R7SA106MB	10±1.0	25±2.0	5.0±0.5	0.6±0.05

Dimensions: mm



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION: C 12/2/2024

ABRACON IS
ISO9001-2015
CERTIFIED

Low ESR, 2.7V Radial Supercapacitor

F 10F 10F 10F
V 2.7V 2.7V 2.7V

ADCR-E02R7S

Request Samples



Check Inventory




Various Sizes

RoHS/RoHS II Compliant


MSL Level = 1

Part Number Identification



*Only part numbers listed in the Electrical Specs table are available. For custom builds, please contact us.

Part Marking



Example of the Markings of a 1.0F 2.7V capacitor

Capacitance (F)

Rated Voltage (V)

Polarity (negative bar on the sleeve to indicate the cathode)



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION: C 12/2/2024

ABRACON IS
ISO9001-2015
CERTIFIED

Low ESR, 2.7V Radial Supercapacitor

F 10F 10F 10F
V 2.7V 2.7V 2.7V

ADCR-E02R7S

Request Samples



Check Inventory




Various Sizes

RoHS/RoHS II Compliant

MSL Level = 1

Wave Profile



Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ 25°C ~ 105°C	60 sec. MAX
	Preheat Rate	$T_{PREHEAT}$ +4°C/Sec MAX	
2	Wave Temperature	T_w 245°C ~ 260°C	10 sec. MAX Dual wave
	Wave Peak Temperature	T_P 260°C	5 sec. MAX/wave
3	Cooling Rate	$T_{COOLING}$	-5°C/Sec MAX



ABRACON

5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION: C 12/2/2024

ABRACON IS
ISO9001-2015
CERTIFIED

Low ESR, 2.7V Radial Supercapacitor

F 10F 10F 10F
V 2.7V 2.7V 2.7V

ADCR-E02R7S

Request Samples



Check Inventory



Various Sizes

RoHS/RoHS II Compliant

MSL Level = 1

Packaging

Part Number	Quantity (PCS/Tray)
ADCR-E02R7SA504MB	180
ADCR-E02R7SA105MB	180
ADCR-E02R7SB105MB	160
ADCR-E02R7SA205MB	120
ADCR-E02R7SA335MB	120
ADCR-E02R7SA505MB	100
ADCR-E02R7SB505MB	120
ADCR-E02R7SA605MB	120
ADCR-E02R7SA705MB	120
ADCR-E02R7SA106MB	80

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf (COTS, which are designed, intended and validated for use in commercial, industrial and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



ABRACON

5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION: C 12/2/2024

ABRACON IS
ISO9001-2015
CERTIFIED