



PRODUCT DESCRIPTION

Tgrease™ 300X is a silicone-based thermal grease for use with high performance CPUs, GPUs, custom ASICs, Multi-Chip, SoC, etc. It has a high thermal conductivity of 3.0 W/mK and superior wetting characteristics, resulting in very low thermal resistance and excellent long-term reliability. Tgrease™ 300X has been formulated with a high thixotropic index. It does not sag or drip enabling easier pump and syringe dispensing. Tgrease™ 300X is ideal for automatic dispensing and screen-printing.

FEATURES & BENEFITS

- 3.0 W/mK bulk thermal conductivity
- Low thermal resistance
- Resists pump out through novel gel technology
- Fully characterized long term reliability
- Unique formulas will not harden, dry out, settle, or oxidize.
- Environmentally friendly solution that meets regulatory requirements including RoHS and REACH

MARKETS

- Semiconductor Packaging
- Graphics Card
- Notebooks
- Desktops
- Servers
- IGBTs
- Automotive
- Memory Modules

AVAILABILITY

- Available in 1kg (quart container), cartridges and custom syringes

STORAGE CONDITIONS

- Store 15°C to 45°C & maximum 50% RH
- Shelf Life unopened: 2 year from date of mix when stored at above conditions

TYPICAL PROPERTIES

PROPERTY	VALUE	TEST METHOD
Construction	Silicone Thermal Grease	N/A
Color	Grey	Visual
Density	2.7 g/cc	Helium Pycnometer
Bulk Thermal Conductivity	3.0 W/m-K	Hot Disk
Thermal Resistance		
10 psi & 50°C	0.20°C-cm²/W	ASTM D5470
50 psi & 50°C	0.12°C-cm²/W	
Operating Temperature Range	-40°C to 150°C	Laird Test Method
Viscosity	400,000 cP	Brookfield Viscometer - TF spindle at 20rpm (helipath) at 23°C
Thixotropic Index	3.35	Brookfield Viscometer
Minimum Bond Line Thickness	25 µm	Laird Test Method
Outgassing (TML)	0.07%	E595
Outgassing (CVCM)	0.01%	E595
Dielectric Constant	28.3@1KHz / 31.8@1MHz	ASTM D150
Dissipation Factor	0.014@1KHz / 0.005@1MHz	ASTM D150
Volume Resistivity	1.0x10 ¹⁴ Ω-cm	ASTM D991

USA: +1.866.928.8181
Europe: +49.8031.24600
Asia: +86.755.2714.1166
www.laird.com



THR-DS-Tgrease 300X 08032022

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user. Laird Technologies makes no warranties as to the fitness, merchantability, suitability or non-infringement of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2020 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc., or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights.