





NOTES:

1. FOR USE WITH NORTHROP NAI-1311 & RG-115A/JTM CABLE.
2. FOR CABLING INSTRUCTIONS SEE CP-480.
3. FOR CABLE TRIMMING USE KTV-137 & KTD-202.
4. FOR FORMING USE CRIMP DIE SIZE 04.
5. THIS ITEM IS IN COMPLIANCE WITH THE APPLICABLE PORTIONS OF SPECIFICATION MIL-C-39012.

UNLESS OTHERWISE SPECIFIED:

- | | |
|---|--|
| 1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS $\pm .010$ | 2. REMOVE ALL BURRS. BREAK SHARP EDGES .005 MAX. |
| 3 PLACE DECIMALS $\pm .004$ | 3. NO FILLETS PERMITTED. |
| 4. T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES. | 4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX. |
| | 5. ALL DIMENSIONS PRIOR TO PLATING. |



9	1	OUTER CONTACT	
8	1	GASKET	
7	1	COUPLING NUT	
6	1	C-RING	
5	1	NCAPTIVE CRIMP CONTACT N	1-547-12
4	1	INSULATOR	
3	1	K-GRIP BODY	
2	1	K-GRIP SLEEVE	N-59-202-1
1	1	GASKET	N-59-260-2
ITEM	REQ'D	DESCRIPTION	PART NO.

REVISIONS

FIGURE	CHANGES
0	SR 14107 JL 18 JAN 75
1	CN 14174 A MJB 2-4-75
2	CN 26178 C CT - 5-30-84
3	CN 38586 E TML 10/02/82

USED ON:

REP:

FINISH:

SPEC:

MATL:

SPEC:

N PLUG

DRAWN JL DATE 18 JAN 75

APPR. LI DATE 18 JAN 75

KINGS ELECTRONICS
40 MARBLEDALE ROAD
TUCKAHOE, N. Y. 10707

KN-59-260

S-D