

Part Number : [1203410505](#)

Product Description : Micro-Change (M12) to Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, X-Coded, Male (Straight) to Male RJ-45 (Straight), 26 AWG, Green Shielded PUR Cable, 5.0m (16.40') Length

Series Number : 120341

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : E26E06020M050



Documents & Resources

Drawings

[1203410505_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; 6,6'-Di-tert-butyl-2,2'-methylenedi-p-cresol per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120341
Description	Micro-Change (M12) to Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, X-Coded, Male (Straight) to Male RJ-45 (Straight), 26 AWG, Green Shielded PUR Cable, 5.0m (16.40') Length
IP Rating	IP20, IP67 (M12 only)
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A,RJ45,Industrial Ethernet
Protocol	EtherNet
Type	Double Ended
UPC	887191128085

Agency

UL	E361772
----	---------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	30V AC (RMS) / 42V DC

Physical

Cable Diameter	6.90mm (.272")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Green
Connector End A	Micro-Change (M12)
Connector End B	RJ-45 (standard)
Coupling Style	Threaded
Gender	Male-Male
Keyway	X-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	7351.550/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Shielded PUR
Wire Size (AWG)	26

This document was generated on Sep 25, 2025