Product Details for 1064353 -1

No Image Available

1064353 -1

Active

RF Coax Cable Assemblies

RoHS Compliant (Statement of Compliance)

Product Highlights:

- 2 Connectorized Ends
- OSMT Application
- Connector Type = OSMT Right Angle Jack
- Assembly Length = 100.00 mm

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- OSMT RIGHT ANGLE JACK TO JACK CABLE ASSY, 180 DEGREE... (PDF, English)

Catalog Pages/Data Sheets:

- RF COAXIAL SOLUTIONS FOR COMMUNICATIONS (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Connector Type = OSMT Right Angle Jack
- Dielectric Material = Polypropylene
- Shield Material = Copper Wire
- Comment = 180° offset

Electrical Characteristics:

- Frequency = DC to 6 GHz
- Connector Impedance (?) = 50
- Voltage (VAC) = 250
- Insulation Resistance (M?) = 1,000

Body Related Features:

- Number of Connectorized Ends = 2
- Assembly Length (mm [in]) = 100.00 [3.940]
- Conductor Material = Copper clad Steel
- Conductor Plating = Tin
- Jacket Material = PVC
- Shield Plating = Tin

Contact Related Features:

- Contact Material = Beryllium Copper
- Contact Mating Area Plating = Gold over Nickel

Configuration Related Features:

- Conductor (Wire) Size = 30 AWG

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application = OSMT

Other:

- Brand = AMP

© 2006 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.