





	1	2	3	4	5	6	7																																																																																			
A		P.C.B. LAYOUT  N=Number of contacts			Material Terminal body (Contact pin): Brass Wire guard: Stainless steel Surface of solder tail: Tin plated Insulator (housing): Thermoplastic (UL94V-0),Green			A																																																																																		
B					Electrical cULus/VDE Voltage rating: 300VAC/250VAC Current rating: 10A/10A Wire range: 0.75-1.5mm² Solid wire(AWG): 14-24 Stranded wire(AWG): 14-24 Pull force: Screw: Wire strip length: 6-7mm Withstanding Voltage: 1.6KV/2KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval: 			B																																																																																		
C								C																																																																																		
D									D																																																																																	
E									E																																																																																	
F									F																																																																																	
G	RoHS compliant		<table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>23.01.2008</td><td>N.Schulz</td></tr><tr><td>X.</td><td>±0.50</td><td></td><td></td><td></td><td></td><td>Approved</td><td>28.06.2010</td><td>Hellwig</td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.10</td><td>③</td><td>Update UL</td><td>23.03.2017</td><td>C.Bakula</td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>②</td><td>Update</td><td>28.06.2010</td><td>Alex</td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±1°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.X°</td><td>±X°</td><td>①</td><td>Drawn</td><td>23.01.2008</td><td>N.Schulz</td><td></td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td><td></td></tr></table>		Scale	1:1					Date	Name	Customer-No.	TOLERANCE						Drawn	23.01.2008	N.Schulz	X.	±0.50					Approved	28.06.2010	Hellwig	X.X	±0.30								X.XX	±0.10	③	Update UL	23.03.2017	C.Bakula				DIM	TOL	②	Update	28.06.2010	Alex				X.°	±1°								X.X°	±X°	①	Drawn	23.01.2008	N.Schulz				Angle	TOL	Id.	Modification	Date	Name						Drawing-No. ASS 2466 CO rev03		G
Scale	1:1					Date	Name	Customer-No.																																																																																		
TOLERANCE						Drawn	23.01.2008	N.Schulz																																																																																		
X.	±0.50					Approved	28.06.2010	Hellwig																																																																																		
X.X	±0.30																																																																																									
X.XX	±0.10	③	Update UL	23.03.2017	C.Bakula																																																																																					
DIM	TOL	②	Update	28.06.2010	Alex																																																																																					
X.°	±1°																																																																																									
X.X°	±X°	①	Drawn	23.01.2008	N.Schulz																																																																																					
Angle	TOL	Id.	Modification	Date	Name																																																																																					
H	③  File No.: E349947						Replace Sheet		H																																																																																	
	1	2	3	4	5	6	7																																																																																			