




+ CONNECTORS
COMBO JACKS



✓ Active

TE CONNECTIVITY (TE)
RJ45 OVER USB W/ LED G/Y 30u" Au
[Modular Jacks & Plugs | A-RJ45](#)

6-1775855-3
TE Internal Number: 6-1775855-3

- [EU RoHS Compliant](#)
- [EU ELV Compliant](#)
- Port Configuration** Stacked
- Jack Type** RJ45 over Single USB
- Performance Category** Cat 3
- PCB Mounting Style** Through Hole
- Profile** Standard

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings
Modular Jack RJ45 Stacked Over USB Conn. Dip Type
PDF
English

CAD Files
Customer View Model
2D_DXF.ZIP
English

3D PDF
PDF
3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Jack Type RJ45 over Single USB
- Performance Category Cat 3
- Profile Standard
- Shielded Yes
- LED With
- Grounding Options Panel Ground and PCB Ground
- Product Type Connector
- Panel Stops Without
- Multi-Port Modular Jack No
- Connector Style Jack
- PCB Mounting Orientation Right Angle

Configuration Features

- Port Configuration Stacked
- Jack Configuration 2 x 1
- Keyed No
- Number of PCB Ground Tabs 4
- Number of Positions 8
- Preloaded Yes

Body Features

- Shield Material Brass
- Shield Plating Material Nickel
- Inverted Jack Face No
- Color Black

Contact Features

- Contact Base Material Phosphor Bronze
- Solder Tail Contact Plating Material Gold Flash over Nickel

Termination Features

- Termination Method to PC Board Solder

Mechanical Attachment

- PCB Mounting Style Through Hole
- Panel Mount Retention Without

Housing Features

Housing Material PBT GF

Dimensions

PCB Tail Length 3.5 mm [.138 in]

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Method Tray, Tray/Box

Packaging Quantity 50

Statement of Compliance

Statement of Compliance

PDF