
T1610BF, Block Fork Terminal, 22-16 AWG, #8-10 Stud



By Burndy
Catalog # T1610BF

Uninsulated Block Fork Terminal, 22-16 AWG, #8-10 Stud, Fits Securely into Terminal Blocks

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	22 - 16 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#22 AWG to #18 AWG

Configuration

Connector Type	Block Fork Terminal

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.79 in
Dimension - L Length Overall mm	21
Dimension - Length Overall inch	0.83 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#8 - #10

General

Feature - Barrel Style	Shrouded
Plated	Yes
Product Family	COMPRESSION
Trade Name	HYDENT™
Physical Attribute - Tongue Type	Block Fork
Product Type	Terminal
UPC	781810530825
Type	Fork Tongue
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810530825
UPC 14 Digit GTIN	00781810530825

Logistics

Minimum Pack Quantity	100
Pallet Quantity	1
Carton Quantity	1

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.