Welcome to TE.com, you are viewing information for visitors in United States
CHOOSE ANOTHER SITE
STAY ON THIS SITE

2-440055-3

HPI 2.0MM,HDR,3POS R/A,BLU

TE Internal #: **2-440055-3**
TE Internal Description: **HPI 2.0MM,HDR,3POS R/A,BLU**

PCB Connector Assembly Type : **PCB Mount Header**
PCB Mount Orientation : **Right Angle**
Connector System : **Wire-to-Board**
Number of Positions : **3**
Centerline (Pitch) : **2 mm [.079 in]**

Similar Products

Compatible Parts & Tooling

We are here to help!
Get in touch with our product experts.

CHAT WITH US
EMAIL US
CALL US

Feedback

Documents | Features | Product Compliance

Product Drawings

HPI 2.0MM,HDR,3POS R/A,BLU
HPI 2.0MM,HDR,3POS R/A,BLU English

CAD Files

PCB Design

CAD Models from SnapEDA

3D PDF

3D_CVM_CVM_2-440055-3_B3.pdf 3D

Customer View Model

ENG_CVM_CVM_2-440055-3_B3.2d_dxf.zip
English

ENG_CVM_CVM_2-440055-3_B3.3d_igs.zip
English

ENG_CVM_CVM_2-440055-3_B3.3d_stp.zip
English

Datasheets & Catalog Pages

1-1773713-2_HIGH_PERFORMANCE_INTERCONNECT_QUICK_REFERRENCE_GUIDE_EN

ENG_DS_1-1773713-2_HPI_QRG_EN_0114_1-1773713-2HPI_Connectors_0114.pdf English

Product Specifications

Product Specification

ENG_SS_108-57100_D.pdf English

Qualification Test Report

[illegible]1-57058_B.pdf English

Downloaded from Arrow.com.

Agency Approvals

UL

ENG_AAD_UL_E28476_20001207__C.pdf

English

UL Report

ENG_AAD_UL_CERT_ML_E186634_E28476_2000120_A.pdf English

CSA Certificate

ENG_AAD_CSA_222156_6233_1475575_A.pdf

English

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

PCB Connector Assembly Type : **PCB Mount Header**
Connector System : **Wire-to-Board**
Header Type : **Partially Shrouded**
Sealable : **No**
Connector & Contact Terminates To : **Printed Circuit Board**
Wire/Cable Type : **Discrete Wire**

Configuration Features

PCB Mount Orientation : **Right Angle**
Number of Positions : **3**
Number of Rows : **1**

Electrical Characteristics

Operating Voltage (VAC): **250**
Operating Voltage (VDC): **250**

Contact Features

Contact Base Material : **Brass**
PCB Contact Termination Area Plating Material : **Tin**
Contact Shape : **Square**
Contact Mating Area Plating Material : **Tin**
Contact Mating Area Plating Material Finish : **Bright**
Contact Mating Area Plating Material Thickness : **2.032 µm [80 µin]**
Contact Type : **Pin**
Contact Current Rating (Max) (A): **3**
PCB Contact Termination Area Plating Material Finish : **Bright**
Mating Post Length : **3.5 mm [.138 in]**

Termination Features

Termination Method to Printed Circuit Board : **Through Hole**
Termination Method to Wire & Cable : **Crimp**
Termination Post & Tail Length : **3.4 mm [.134 in]**
Terminations per Post (Max) : **3**

Mechanical Attachment

PCB Mount Retention Type : **Kinked Tines**
Contact Retention Type : **Locking Lance**
PCB Mount Alignment : **Without**
Mating Retention : **Without**
PCB Mount Retention : **With**
Connector Mounting Type : **Board Mount**
Contact Retention : **With**

Downloaded from Arrow.com.

Housing Features	Centerline (Pitch) : **2 mm [.079 in]** Housing Color : **Blue** Housing Material : **Nylon 66 GF**
Dimensions	Wire Size (AWG): **30 – 24** Accepts Wire Insulation Diameter Range : **.9 mm [.0354 – .059 in]** PCB Thickness (Recommended) : **1 – 1.6 mm [.039 – .063 in]** Length : **8 mm [.314 in]** Height : **4.95 mm [.1949 in]** Width : **7.7 mm [.303 in]**
Usage Conditions	Operating Temperature Range : **-25 – 85 °C [-13 – 185 °F]**
Operation/Application	Circuit Application : **Signal**
Industry Standards	UL Flammability Rating : **UL 94V-0**
Packaging Features	Packaging Quantity : **250** Packaging Method : **Bag**
EU RoHS Directive 2011/65/EU	*This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).*
EU ELV Directive 2000/53/EC	
China RoHS 2 Directive MIIT Order No 32, 2016	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: **JAN 2019 (197)** Candidate List Declared Against: **JUN 2013 (144)**
Halogen Content	
Solder Process Capability	Wave solder capable to 240°C
Statement of Compliance	Statement of Compliance pdf

Downloaded from Arrow.com.

Compliance Documents	There may be Environmental Compliance related documents on the DOCUMENTATION Tab

Disclaimer	This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Products with Similar Specs

View All Similar Products

THIS PRODUCT

WIRE-TO-BOARD HEADERS &...
2-440055-3
HPI 2.0MM, HDR, 3POS R/A, BLU

Non-Stocked

TOP RESULTS

WIRE-TO-BOARD HEADERS &...
4-440055-3
HPI 2.0MM, HDR, 3POS R/A, YEL

Non-Stocked

WIRE-TO-BOARD HEADERS &...
8-440055-3
HPI 2.0MM, HDR, 3POS R/A, RED

Non-Stocked

WIRE-TO-BOARD HEADERS &...
6-440055-3
HPI 2.0MM, HDR, 3POS R/A, BLK

Non-Stocked

Downloaded from Arrow.com.

PCB Connector Assembly Type : **PCB Mount Header**
PCB Mount Orientation : **Right Angle**
Connector System : **Wire-to-Board**
Number of Positions : **3**

PCB Connector Assembly Type : **PCB Mount Header**
PCB Mount Orientation : **Right Angle**
Connector System : **Wire-to-Board**
Number of Positions : **3**

PCB Connector Assembly Type : **PCB Mount Header**
PCB Mount Orientation : **Right Angle**
Connector System : **Wire-to-Board**
Number of Positions : **3**

PCB Connector Assembly Type : **PCB Mount Header**
PCB Mount Orientation : **Right Angle**
Connector System : **Wire-to-Board**
Number of Positions : **3**

Downloaded from Arrow.com.