Part Number : 2005010121
Product Description : stAK50h Vertical Hybrid Header, 12 Circuits, Key 1, Black, Tube
Series Number : 200501
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2005010121_sd.pdf

2005058100-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2005060000-AS-000.pdf

2005060000-AS-CH-000.pdf

1600140001-000.pdf

2005060001-PS-000.pdf

2005060001-PS-CH-000.pdf

2005000120-TS-000.pdf

2005010120-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC

Downloaded from Arrow.com.

Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	200501
Description	stAK50h Vertical Hybrid Header, 12 Circuits, Key 1, Black, Tube
Application	Automotive, Wire-to-Board
Component Type	PCB Header
Product Name	stAK50h
UPC	889056679411

Electrical

Current - Maximum per Contact	12.0A, 30.0A
Voltage - Maximum	14V DC

Physical

Downloaded from Arrow.com.

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	6.782/g
Number of Rows	4
Orientation	Vertical
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	4.00mm, 7.20mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	Yes
Temperature Range - Operating	-40° to +105°C LV-214, -40° to +85°C GMW3191 June2012
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number

Downloaded from Arrow.com.

stAK50h Hybrid Receptacle, 12 Circuits, Key 1, Black, Bag	1600260001

This document was generated on Jun 02, 2026

Downloaded from Arrow.com.