



**STRAIGHT RECEPTACLE FOR PRINTED CIRCUIT
PACKAGING BY100 SELECTIVE TIN PLATE**
R141.508.200
SERIES BNC


	MM		INCH	
	maxi	mini	maxi	mini
A	1.3	1.1	0.051	0.043
B	1.7	1.5	0.067	0.059
C	8.65	8.55	0.341	0.337

NOMINAL IMPEDANCE	50 Ω
FREQUENCY RANGE	0-4 GHz
TEMPERATURE RATING	-65/+165 °C
V.S.W.R	NA + 0 x F(GHz)Maxi
RF INSERTION LOSS	NA $\sqrt{F}$ (GHz) dB Maxi
VOLTAGE RATING	500 Veff Maxi
DIELECTRIC WITHSTANDING VOLTAGE	1500 Veff Mini
INSULATION RESISTANCE	5000 M Ω Mini
HERMETIC SEAL	NA Atm.cm ³ /s
LEAKAGE (pressurized only)	NA
MECHANICAL DURABILITY	Cycles
WEIGHT	4.91 gr
SPECIFICATION	

CABLES :

OTHERS CHARACTERISTICS

CABLE RETENTION	NA	N Mini
CENTER CONTACT RETENTION		
Axial force - mating end	18.1	N Mini
Axial force - opposite end	NA	N Mini
Torque	NA	cm.N Mini
RECOMMENDED TORQUES		
Mating	NA	cm.N
Panel nut	NA	cm.N
Clamp nut	NA	cm.N

CONNECTOR PARTS MATERIALS

BODY	BRASS
OUTER CONTACT	
CENTER CONTACT	BRASS
INSULATOR	PTFE
GASKET	
OTHERS PIECES	

FINISH (all values are given in micrometers)

NICKEL + SELECTIVE TIN PLATE
SILVER 5 OVER COPPER 0.5
-
-

ISSUE	CREATION DATE	FILE PART-NUMBER
9707A00	16-MAY-91	91-0400-173



The information given here is subject to change without notice.
Design changes may be in order to improve the product.

Connect to the future