

AR0144CS

CMOS Image Sensor, Digital, Global Shutter, 1.0 MP, 1/4-Inch

Product Overview

For complete documentation, see the data sheet.

The AR0144 is a 1/4-inch 1.0 Mp CMOS digital image sensor with an active-pixel array of 1280H x 800V. It incorporates a new innovative global shutter pixel design optimized for accurate and fast capture of moving scenes. The sensor produces clear, low noise images in both low-light and bright scenes. It includes sophisticated camera functions such as auto exposure control, windowing, row skip mode, column-skip mode, pixel-binning and both video and single frame modes. It is programmable through a simple two-wire serial interface. The AR0144 produces extraordinarily clear, sharp digital pictures, and its ability to capture both continuous video and single frames makes it the perfect choice for a wide range of applications, including scanning and industrial inspection.

Features

- Best Global Shutter Efficiency
- Low Dark Current/Hot Pixels
- High Linear Full Well
- Low Operational Power
- Small Form Factor

Applications

- Barcode Scanning
- 3D Scanning
- Virtual/Augmented Reality
- Positional Tracking
- Gesture Recognition

End Products

- Barcode Scanners
- Head Mounted Displays
- Biometric Scanners
- Virtual Reality/Augmented Reality Glasses
- Drones

Part Electrical Specifications

Product	Status	Compliance	Type	Mega-pixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Output Interface	Color	Family	Packaging Type	Cas e Outline	MS L Type	MS L Temp (°C)	Container Type	Container Qty.
AR0144CSSC00 SUD20	Obsolete		CMOS	-	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	RGB	-	-		NA	0	MTFRM	1
AR0144CSSC00 SUKA0-CPBR	Active		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	RGB	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	3000
AR0144CSSC00 SUKA0-CRBR	Obsolete		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	RGB	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	3000
AR0144CSSC20 SUD20	Active		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	RGB	-	-		NA	0	MTFRM	1
AR0144CSSC20 SUKA0-CPBR	Active		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	RGB	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	3000
AR0144CSSC20 SUKA0-CRBR	Active		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	RGB	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	3000
AR0144CSSM0 SUD20	Obsolete		CMOS	-	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	Monochrome	-	-		NA	0	MTFRM	1
AR0144CSSM0 SUKA0-CPBR	Active		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	Monochrome	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	3000
AR0144CSSM0 SUKA0-CRBR	Active		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	Monochrome	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	3000
AR0144CSSM2 SUD20	Last Shipments		CMOS	-	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	Monochrome	-	-		NA	0	MTFRM	1
AR0144CSSM2 SUKA0-CPBR	Active		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	Monochrome	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	3000
AR0144CSSM2 SUKA0-CPBR1	Last Shipments		CMOS	-	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	Monochrome	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	300
AR0144CSSM2 SUKA0-CRBR	Active		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	Monochrome	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	3000
AR0144CSSM2 SUKA0-CRBR1	Obsolete		CMOS	-	60	1/4 inch	Global Shutter	3.0 x 3.0	Multi	Monochrome	-	OD CSP -69	570 BV. PDF	4	245	CTRAY	300
AR0144CSSM2 8SUD20	Active		CMOS	1	60	1/4 Inch	Global Shutter	3.0 x 3.0	Multi	Monochrome	-	-		NA	0	MTFRM	1
AR0144CSSM2 8SUKA0-CPBR	Active		-	1	-	-	-	-	-	-	-	OD CSP -69	570 BV. PDF	5	260	CTRAY	3000