




Part Number : [788610003](#)

Product Description : 1.27mm Signal Pitch,
0.80mm Signal Pitch, 1.27mm Power Pitch
SAS-3 Receptacle, Right-Angle, Surface Mount,
with Forklock, 0.93mm Height, 2.50mm Peg
Length, 1.60mm PCB Thickness, 29 Circuits,
Embossed Tape and Reel, Lead-Free

Series Number : 78861

Status : Active

Product Category : I/O Connectors



Documents & Resources

Drawings

[Drawing 788610003_sd.pdf](#)

[Packaging Design Drawing PK-78861-001-001.pdf](#)

3D Models and Design Files

[3D Model 788610003_stp.zip](#)

Specifications

[Product Specification PS-78861-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	I/O Connectors
Series	78861
Description	1.27mm Signal Pitch, 0.80mm Signal Pitch, 1.27mm Power Pitch SAS-3 Receptacle, Right-Angle, Surface Mount, with Forklock, 0.93mm Height, 2.50mm Peg Length, 1.60mm PCB Thickness, 29 Circuits, Embossed Tape and Reel, Lead-Free
Application	Board-to-Board
Comments	Without Cap
Component Type	Receptacle
Product Family	Serial Attached SCSI (SAS) Connectors
Product Name	SAS 12G,SAS-3
Type	N/A
UPC	889056133807

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Physical

Circuits Detail	Signal 14, Power 15
-----------------	---------------------

Circuits (Loaded)	29
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	1.764/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	0.80mm, 1.27mm
Pitch - Termination Interface	0.80mm, 1.27mm
Plating min - Mating	0.762μm
Plating min - Termination	2.540μm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	0° to +55°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	SFF-8482 and SFF-8680 Plugs, SAS / SATA Plugs

This document was generated on Dec 09, 2023
