

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	23JUN2020	JA	TD
	A1	ECR-23-183736	22AUG2023	PC	TD






LOOSE PIECE CONFIGURATION
4-2322343-( )

TERMINALS TO UNWIND FROM REELS AS SHOWN

2322343-( )



NOTES

1. SPECIFICATION
MAGNET WIRE 0.40-1.20mm ALUMINUM WIRE
0.3-0.8mm² STRANDED,BONDED OR SOLID WITH PVC INSULATION.
MAXIMUM INSULATION OUTSIDE DIAMETER IS 2.90mm,NO STRIPPING REQUIRED.

2 POCKET RECOMMENDATION
1601421 FOR SINGLE TERMINAL
1601433 FOR DOUBLE BUSSED TERMINALS
1601440 FOR TRIPLE BUSSED TERMINALS

3. TERMINAL APPLICATION TO COMPLY WITH TE CONNECTIVITY SPECIFICATION 114-13166, FIG. 3

2322343-2
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±2°

MATERIAL: BRASS SPRING HARD
FINISH: POST TIN -

DWN 08NOV2018 JUSTIN HUANG
CHK 08NOV2018 TIM DING
APVD 08NOV2018 SENTHIL KUMAR
PRODUCT SPEC 108-2085
APPLICATION SPEC - (3)
WEIGHT -

TE Connectivity

NAME
WIRE TO WIRE,STD
SIAMEZE TERMINAL FOR AL WIRE
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2322343	-

CUSTOMER DRAWING | SCALE 10:1 | SHEET 1 OF 1 | REV A1

1470-19 (3/13)

Downloaded from Arrow.com.