

Data Sheet | Item Number: 221-942

Jumper; for conductor entry; 2-way; insulated; dark gray

<https://www.wago.com/221-942>



Color: ■ dark gray



Electrical data

Rated current	41 A
---------------	------

Physical data

Width	12.3 mm / 0.484 inches
Height	3.8 mm / 0.15 inches
Depth	23.9 mm / 0.941 inches



Material data		
Color		dark gray
Insulation material (main housing)		Polyamide (PA66)
Weight of insulation material		0.28 g
Weight		2.7 g

Commercial data		
PU (SPU)		5 pcs
Packaging type		Bag
Country of origin		CN
GTIN		4055144067965
Customs tariff number		85366990990

Product Classification		
UNSPSC		39121421
ETIM 9.0		EC000489
ETIM 10.0		EC000489
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption


Environmental requirements		
Continuous operating temperature from		-60 °C
Continuous operating temperature up to		105 °C
Continuous operating temperature		-60 ... +105 °C

Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 221-942		


Documentation		
Bid Text		
221-942	docx 27.51 KB	
221-942	xml 2.96 KB	

CAD/CAE-Data**CAD data**

2D/3D Models 221-942

**Installation Notes****Commoning**


Extending the N and PE (ground) distribution via jumper

Commoning

Insert the jumper without a locking function into open clamping units.

Commoning

Without a locking function:
The jumper without a locking function is plugged into the splicing connectors.

Commoning

Remove the jumper from open clamping units.