








8x **A** common tolerances zone
 $\square \pm 0.05$



P.C. LAYOUT



SCHEMATIC




Compliance: RohS II (2011/65/EU)

Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm above 50-100: ±0.5mm			Date	Name	MMS 228 T		
			09/07	dr			
Dimension	07/16	dr					
Coplanarity	06/16	dr					
Material contact plate	07/14	dr					
Soldering conditions	07/11	dr					
Slider position	06/10	dr					
Dimensions	07/09	dr			30 12 35		
Material	06/09	dr	knitter-switch				
Operating temperature	11/07	dr					
Material	09/07	dr					
Modifications	Date	Name				Page 1/3	

Specifications:

Contact rating: 200mA, 12V DC / 300mA, 6V DC (100mA, 24V DC)
Contact resistance: 70mOhm max.
Insulation resistance: 100MOhm min. at 500V DC
Dielectric strength: 500V, 50Hz for the duration of 1 minute
Operating temperature: -10°C to +60°C
Mechanical life: 10 000 cycles min.
Contact timing: non-shorting
Switching function: on - on
Material: Terminal: brass strip, silver plated
Cover: SUS, washing
Slider: PA46, blue
Contact plate: stainless steel, silver plated
Case: PA46, black


Soldering conditions:



Compliance: RohS II (2011/65/EU)

Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm above 50-100: ±0.5mm			Date	Name	MMS 228 T	
			09/07	dr		
			knitter-switch		30 12 35	Page
						2/3
Modifications	Date	Name				

Packaging:



Packaging unit: 900 pcs. / reel
Compliance: RohS II (2011/65/EU)

Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm above 50-100: ±0.5mm			Date	Name	MMS 228 T		
			09/07	dr			
			knitter-switch		30 12 35		Page
							3/3
Modifications	Date	Name					