

Part Number : [192210408](#)

Product Description : Compression Style Ring tongue Terminal for 8 AWG Wire, Stud Size 10 (M5), Unplated, Carton

Series Number : 19221

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : BCL-810



Documents and Resources

Drawings

[192210408 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19901-017-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19221
Description	Compression Style Ring tongue Terminal for 8 AWG Wire, Stud Size 10 (M5), Unplated, Carton
Comments	Heavy Duty
Keyword	Ring Terminal, Ring Terminals
Product Name	Battery Cable Lug
Style	Ring, Unplated
Type	Battery Cable Lug
UPC	800753064928

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Unplated
Net Weight	5.189/g

Packaging Type	Carton
Stud Size	10 (M5)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size (AWG)	8
Wire Size mm ²	8.36

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG	<u>192840034</u>

This document was generated on Apr 26, 2026