

HONEYWELL
PART NUMBER
4

REV	DOCUMENT	CHANGED BY	CHECK
A	0016254	KSR 27OCT05	RJ

(ILLUMINATED: 1=CLEAR AMBER, 2=CLEAR RED, 3=CLEAR BLUE, 4=CLEAR GREEN, 5=CLEAR)

ACTUATOR COLOR 7
(NON-ILLUMINATED: B=BLACK, W=WHITE)

NUMBER OF POLES 5
(1=SP-SINGLE POLE, 2=DP-DOUBLE POLE)

CIRCUITRY 5


BASE/BEZEL COLOR
(B=BLACK, W=WHITE)

LAMP/ELECTRICAL RATING 6

TERMINAL STYLE


.187 WIDE QUICK
CONNECT TABS

CODE 6	LAMP	RATING
N	NON-ILLUMINATED	8A, 250VAC 12A, 125VAC 1/2 HP, 125-250VAC UL, CSA
I	UNBALLASTED LED	N/A
2	6V LED	12A, 6V
3	12V LED	12A, 12V
4	24V LED	12A, 24V
A	6V INCANDESCENT	12A, 6V
C	12V INCANDESCENT	12A, 12V
E	18V INCANDESCENT	12A, 18V
H	24V INCANDESCENT	12A, 24V
J	125V NEON	12A, 125VAC UL, CSA
K	250V NEON	8A, 250VAC UL, CSA



PANEL THICKNESS	A	B
.030[.76]-.050[1.27]	.508[12.90]	.756[19.20]
.050[1.27]-.078[1.98]	.508[12.90]	.764[19.40]
.078[1.98]-.125[3.17]	.508[12.90]	.780[19.81]

CIRCUIT DIAGRAMS 5



RECOMMENDED
PANEL
OPENING

A +.004[.10]
-.000[.00]

B +.000[.00]
-.004[.10]

- 1 - OPERATING TEMPERATURE RANGE : 32°F TO 185°F
- 2 - ELECTRICAL LIFE : 50,000 CYCLES
- 3 - MECHANICAL LIFE : 100,000 CYCLES
- 4 SEE DIAGRAM FOR CATALOGING SCHEME
- 5 REFER TO APPLICABLE CIRCUIT DIAGRAM
- 6 REFER TO TABLE FOR SPECIFIC LAMPS AND ELECTRICAL RATINGS
- 7 CLEAR BLUE ACTUATOR ONLY AVAILABLE WITH INCANDESCENT LAMPS

DESIGN UNITS: INCH	
TOLERANCES UNLESS NOTED:	
NO PLACE	X ± 0.040
ONE PLACE	.X ± 0.030
TWO PLACE	.XX ± 0.015
THREE PLACE	.XXX ± 0.005
FOUR PLACE	.XXXX ± 0.0005
ANGLES	X ± 2

THIRD ANGLE PROJECTION



DRAWN	NM	13 JUN 05
CHECK	RJ	27OCT05
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

Honeywell			
TITLE SWITCH , ROCKER			
SIZE B	TYPE I	DRAWING NAME MR SERIES CHART 1	REV A
SCALE -	SHEET 1 OF 1		