



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1		*FIRST RELEASED*	Apr.05,2016	Drack	Tommy









KEY	*PART NUMBER*	
	-40°C ~ 105°C	*-40°C ~ 125°C*
N	RTS612NDCG	RTS612NDCG03

NOTES : (UNLESS OTHERWISE SPECIFIED)

1. *MATERIAL :*
   SHELL : THERMOPLASTIC , UL94 V-0.
   SEAL GASKET : NBR OR SR.
2. *SPECIFICATIONS :*
   2.1, OPERATING TEMPERATURE : SEE TABLE.
   2.2, IP-CLASS : IP67.
   2.3, MATING CYCLES DURABILITY : 500 CYCLES MIN.
   2.4, RoHS COMPLIANT.
3. *ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.*

QUANTITY	*PART NUMBER*	DESCRIPTION	ITEM

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED
1) All dimensions are in metric(mm).
2) Tolerances are as follows:
2 PL DEC ±0.15
3 PL DEC ±0.08
Fractions ±1/64
Angles ±1°
3) Note reference = X

MATERIAL SPECIFICATIONS:

PROCESS SPECIFICATIONS:

NEXT ASS'Y:

SIGNATURES		*DATE*
DRAWN:	Drack	Apr.05,2016
CHECKED:		
ENGINEER:		
APPROVAL:		
CUSTOMER:		

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Amphenol
Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036

ECO-MATE,DUST CAP,PLUG
SIZE 12

SIZE	TYPE	DWG NO:	REVISION
B	C-	RTS612*DCGxx	A1

SCALE: NONE SHEET 1 OF 1

TITLE: *ECO-MATE,DUST CAP,PLUG,SIZE 12*
DWG NO: RTS612*DCGxx
REV: A1
SH: 1
OF: 1

Downloaded from Arrow.com.