



SPECIFICATION (Reference sheet)

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor
- Samsung P/N : CL32B106MOJNNNE
- Description : CAP, 10 μ F, 16V, $\pm 20\%$, X7R, 1210

A. Samsung Part Number

CL 32 B 106 M O J N N E
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① Series	Samsung Multi-layer Ceramic Capacitor		
② Size	1210 (inch code)	L: 3.2 \pm 0.3 mm	W: 2.5 \pm 0.2 mm
③ Dielectric	X7R	⑧ Inner electrode	Ni
④ Capacitance	10 μ F	Termination	Cu
⑤ Capacitance tolerance	$\pm 20\%$	Plating	Sn 100% (Pb Free)
⑥ Rated Voltage	16 V	⑨ Product	Normal
⑦ Thickness	2.5 \pm 0.2 mm	⑩ Special	Control code
		⑪ Packaging	Embossed Type, 7" reel

B. Samsung Reliability Test and Judgement condition

	Performance	Test condition	
Capacitance	Within specified tolerance	1kHz $\pm 10\%$	1.0 ± 0.2 VRms
Tan δ (DF)	0.1 max.		
Insulation Resistance	10,000Mohm or 100Mohm· μ F Whichever is Smaller	Rated Voltage	60~120 sec.
Appearance	No abnormal exterior appearance	Microscope ($\times 10$)	
Withstanding Voltage	No dielectric breakdown or mechanical breakdown	250% of the rated voltage	
Temperature Characterisitcs	X7R (From -55°C to 125°C, Capacitance change shoud be within $\pm 15\%$)		
Adhesive Strength of Termination	No peeling shall be occur on the terminal electrode	500g·F, for 10 ± 1 sec.	
Bending Strength	Capacitance change : within $\pm 12.5\%$	Bending to the limit (1mm) with 1.0mm/sec.	
Solderability	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder 245 ± 5 °C, 3 ± 0.3 sec. (preheating : 80~120°C for 10~30sec.)	
Resistance to Soldering heat	Capacitance change : within $\pm 7.5\%$ Tan δ , IR : initial spec.	Solder pot : 270 ± 5 °C, 10 ± 1 sec.	

Performance		Test condition
Vibration Test	Capacitance change : within $\pm 5\%$ Tan δ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours \times 3 direction (x, y, z)
Moisture Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.125 max IR : $12.5\text{M}\Omega \cdot \mu\text{F}$ or Over	With rated voltage $40 \pm 2^\circ\text{C}$, 90~95%RH, 500+12/-0hrs
High Temperature Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.125 max IR : $25\text{M}\Omega \cdot \mu\text{F}$ or Over	With 150% of the rated voltage Max. operating temperature 1000+48/-0hrs
Temperature Cycling	Capacitance change : within $\pm 7.5\%$ Tan δ , IR : initial spec.	1 cycle condition Min. operating temperature $\rightarrow 25^\circ\text{C}$ \rightarrow Max. operating temperature $\rightarrow 25^\circ\text{C}$ 5 cycle test

C. Recommended Soldering method :

Reflow (Reflow Peak Temperature : $260 \pm 0/-5^\circ\text{C}$, 10sec. Max)

 Product specifications included in the specifications are effective as of March 1, 2013.
Please be advised that they are standard product specifications for reference only.
We may change, modify or discontinue the product specifications without notice at any time.
So, you need to approve the product specifications before placing an order.
Should you have any question regarding the product specifications,
please contact our sales personnel or application engineers.